



ZC12A2B0000-F008

InstaPATCH® ZERO Cord Cassette with twelve Category 6A U/UTP patch cords, light blue jacket, tail length 8 feet

Configuration Specifications

ANSI/TIA Category	6A
Cable Types	U/UTP (unshielded)
Jacket Color, copper	Light blue
Interface Feature, copper connector A	Standard
Interface Feature, copper connector B	Standard
Interface, copper connector A	RJ45 plug
Interface, copper connector B	RJ45 plug
Port Quantity, copper	12

Dimensions

Tail Length	2.4 m 8.0 ft
Connection Range, overhead	914.4 mm 36.0 in
Depth	711.2 mm 28.0 in
Height	289.6 mm 11.4 in
Weight	8.16 kg 18.00 lb
Width	43.7 mm 1.7 in

Environmental Specifications

Safety Standard	CE cETL ETL
-----------------	-----------------

General Specifications

Brand	InstaPATCH® ZERO SYSTIMAX®
Color	Black
Finish	Powder-coated, smooth
Ordering Note	Available in Mexico, Central America, and South America Available in the United States and Canada
Package, quantity	1

Mechanical Specifications

Material Type	Plastic Steel
---------------	-----------------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

ZC12A2B0000-F008



Included Products

860474253 | 1095B LB 4/24 RVAR (Product Component—not orderable) — GigaSPEED® X10D 1095B Category 6A U/UTP Cable, non-plenum, light blue jacket, 4 pair count, variable length, reel