



## ZC12A3B0000-F006

**InstaPATCH® ZERO Cord Cassette with twelve Category 6A U/UTP patch cords, dark gray jacket, tail length 6 feet**

### Configuration Specifications

ANSI/TIA Category	6A
Cable Types	U/UTP (unshielded)
Jacket Color, copper	Dark gray
Interface Feature, copper connector A	Standard
Interface Feature, copper connector B	Standard
Interface, copper connector A	RJ45 plug
Interface, copper connector B	RJ45 plug
Port Quantity, copper	12

### Dimensions

Tail Length	1.8 m   6.0 ft
Connection Range, overhead	914.4 mm   36.0 in
Depth	711.2 mm   28.0 in
Height	289.6 mm   11.4 in
Weight	7.26 kg   16.00 lb
Width	43.7 mm   1.7 in

### Environmental Specifications

Safety Standard	CE   cETL   ETL
-----------------	-----------------

### General Specifications

Brand	InstaPATCH® ZERO   SYSTIMAX®
Color	Black
Finish	Powder-coated, smooth
Ordering Note	Available in Mexico, Central America, and South America   Available in the United States and Canada
Package, quantity	1

### Mechanical Specifications

Material Type	Plastic   Steel
---------------	-----------------

### Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

ZC12A3B0000-F006



## Included Products

860474246 | 1095B DG 4/24 RVAR (Product Component—not orderable) — GigaSPEED® X10D 1095B Category 6A U/UTP Cable, non-plenum, dark gray jacket, 4 pair count, variable length, reel