



CC0020545/1 | UNJ500-CM

Uniprise UNJ500 Category 5e U/UTP Information Outlet, misty cream

## Dimensions

Depth	30.48 mm   1.20 in
Height	20.32 mm   0.80 in
Width	20.32 mm   0.80 in

## Electrical Specifications

ANSI/TIA Category	5e
Contact Resistance Variation, maximum	20 mOhm
Contact Resistance, maximum	100 mOhm
Current Rating	1.5 A @ 20 °C 1.5 A @ 68 °F
Dielectric Withstand Voltage, RMS, conductive surface	1500 Vac @ 60 Hz
Dielectric Withstand Voltage, RMS, contact-to-contact	1000 Vac @ 60 Hz
Insulation Resistance, minimum	500 MOhm

## Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	cUL   UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

## General Specifications

Brand	Uniprise®
Cable Type	U/UTP (unshielded)
Color	Misty cream
Product Type	Outlet
Package, quantity	1

## Mechanical Specifications

Conductor Gauge, solid	22 AWG   24 AWG   26 AWG
Conductor Gauge, stranded	22 AWG   24 AWG
Conductor Type	Solid   Stranded (7 strands)
Material Type	Copper alloy   High -impact, flame retardant, thermoplastic

CC0020545/1 | UNJ500-CM

Outlet/Module Contact Plating	Precious metals
Plug Insertion Life, minimum	750 times
Plug Insertion Life, test plug	IEC 60603-7 compliant plug
Plug Retention Force, minimum	30 lbf   133 N
Rear Termination Contact Plating	Precious metals
Rear Termination Type	IDC
Wiring	T568A   T568B

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

