



## UC1AAA2-0Z | UNC10G-BL

**Uniprise Ultra 10® Category 6A U/UTP Patch Cord, Snagless, Blue Jacket**

### Dimensions

Cord Length, maximum	100 ft   30 m
Cord Length, minimum	7 ft   2 m

### Electrical Specifications

ANSI/TIA Category	6A
dc Resistance, maximum	0.30 ohm
Safety Voltage Rating	300 V

### Environmental Specifications

Environmental Space	Non-plenum
Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cETL   ETL

### General Specifications

Cable Type	U/UTP (unshielded)
Interface, connector A	RJ45 plug
Interface, connector B	RJ45 plug
Jacket Color	Blue
Brand	Ultra 10®   Uniprise®
Interface Feature, connector A	Standard
Interface Feature, connector B	Standard
Package, quantity	1
Pairs, quantity	4

### Mechanical Specifications

Conductor Type	Solid
Material Type	Copper alloy   Polycarbonate
Outlet/Module Contact Plating	Precious metals
Plug Insertion Life, minimum	750 times
Plug Retention Force, minimum	133 N   30 lbf
Wiring	T568B

### Wiring Diagram

UC1AAA2-0Z | UNC10G-BL

	Connector A	Connector B
Position 1	White/Orange	White/Orange
Position 2	Orange	Orange
Position 3	Lt. Green	Lt. Green
Position 4	Blue	Blue
Position 5	Lt. Blue	Lt. Blue
Position 6	Green	Green
Position 7	Lt. Brown	Lt. Brown
Position 8	Brown	Brown

## Regulatory Compliance/Certifications

### Agency

RoHS 2002/95/EC  
ISO 9001:2008

### Classification

Compliant  
Designed, manufactured and/or distributed under this quality management system



## Included Products

CC8469344 | UNC10G BLUE 4/24 Bulk (Product Component—not orderable) — Ultra 10® 10GNJ4 Category 6A U/UTP Cable, non-plenum, blue jacket, 4 pair count, bulk length, reel