



## UC1DDD2-0Z | UNC5-BL

**Uniprise Category 5e U/UTP Patch Cord, RJ45 to RJ45, 4-pair, Non-Plenum, Blue Jacket**

### Dimensions

Cord Length, maximum	100 ft   30 m
Cord Length, minimum	1 ft   1 m

### Electrical Specifications

ANSI/TIA Category	5e
dc Resistance, maximum	0.30 ohm
Safety Voltage Rating	300 V

### Environmental Specifications

Environmental Space	Non-plenum
Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cETL   ETL

### General Specifications

Cable Type	U/UTP (unshielded)
Interface, connector A	RJ45 plug
Interface, connector B	RJ45 plug
Jacket Color	Blue
Brand	Uniprise®
Interface Feature, connector A	Standard
Interface Feature, connector B	Standard
Package, quantity	1
Pairs, quantity	4

### Mechanical Specifications

Conductor Type	Stranded
Material Type	Copper alloy   Polycarbonate
Outlet/Module Contact Plating	Precious metals
Plug Insertion Life, minimum	750 times
Plug Retention Force, minimum	133 N   30 lbf
Wiring	T568B

### Wiring Diagram

### Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

UC1DDD2-0Z | UNC5-BL



## Included Products

CC4657844/BU | 5EJ4/UNC5 BLUE BULK REEL (Product Component—not orderable) — DataPipe® 5EJ4 Category 5e U/UTP Cable, non-plenum, blue jacket, 4 pair count, bulk length, reel