



6030

### Overview

The 6030 programmable timer is suitable for most functions that require a timed operation e.g. Applications, Siren/Bell Cut Off Module, Dialer Delay, Guard Tour Supervisory Timer, Pulsar / Flasher, etc.

### Specifications

- 6VDC or 12VDC operation is selectable.
- Form "C" relay contacts are 5 amp at 120VAC/28VDC.
- Current draw stand by 3mA relay energizes at 75mA.
- Quick and extremely accurate time range adjustment from 1 second to 60 minutes.
- LED indicates relay is energized.

- Repeat (flasher/pulse) mode.
- Relay activates at the end of the timing cycle.

Board Dimensions: 3"L x 2.5"W x .75"H

#### 6030 weights (approximate):

Product Weight: 0.98 lbs.  
Shipping Weight: 1.0 lbs.

### Board Dimensions (approximate)

3"L x 2.5"W x .75"H

### Mounting Diagram

