

# AL1024ULXPD4(R), AL1024ULXPD4CB(R) Multi-Output Power Supply/Chargers

Rev. DSAL1024ULXPD4 - J18G



#### **Overview**

• These multi-agency approved multi-output power supply/chargers convert a 115VAC/60Hz input to four (4) 24VDC outputs.

#### AL1024ULXPD4

- Fuse protected non-power limited outputs rated @ 3.5 amp each.
- · Grev enclosure.

#### AL1024ULXPD4R

· Red enclosure.

#### AL1024ULXPD4CB

- Class 2 Rated PTC protected power limited outputs rated @ 2.5 amp each.
- · Grey enclosure.

### AL1024ULXPD4CBR

· Red enclosure.

## **Specifications**

- 24VDC outputs.
- 10 amp of continuous supply current for Access Control applications.
- 8 amp of continuous supply current for Fire Alarm applications.
- Four (4) protected outputs.
- Input 115VAC / 60Hz, 4.4 amp.
- Input fuse rated @ 3.5 amp/250V.
- Filtered and electronically regulated outputs.
- Short circuit and thermal overload protection.
- · Built-in charger for sealed lead acid or gel type batteries.

- Maximum charge current 3.6 amp.
- Automatic switch over to stand-by battery when AC fails (zero voltage drop).
- AC fail supervision (form "C" contacts).
- Low battery supervision (form "C" contacts).
- Battery presence supervision (form "C" contacts).
- AC input and DC output LED indicators.
- Enclosure:
  - Combination knockouts are 1/2" and 3/4"
  - Accommodates up to two (2) 12VDC/12AH batteries.

## Agency Approvals



UL 294

UL Listed for Access Control

System Units.

UL 1481 UL Listed Standard for Safety for Fire Protective Signaling Systems.



CUL Listed - CSA Standard C22.2 No.205-M1983, Signal Equipment.

## **Enclosure Dimensions**

15.5"H x 12"W x 4.5"D

