



## ***AL125ULE Multi-Output Power Supply Charger w/Fire Alarm Interface***

Rev. DSAL125ULE - J12G

### **Overview**



- This Altronix power supply converts a 24VAC/40VA input, to a 12VDC @ 1 amp of total supply current or 24VDC @ .5 amp of total supply current Class 2 Rated power limited output.

### **Specifications**

- 12VDC or 24VDC selectable output.
- 1 amp @ 12VDC or 0.5 amp @ 24VDC of supply current.
- Two (2) PTC protected Class 2 Rated power limited outputs.
- Filtered and electronically regulated output.\*
- Short circuit and thermal overload protection.
- Built-in charger for sealed lead acid or gel type batteries.
- Maximum charge current: .4 amp
- Automatic switch over to stand-by battery when AC fails.
- AC power and unit status indicator on the front panel.
- Normally Open [NO] trigger input.
- Supervised Fire Alarm Disconnect (Latching w/reset or Non-Latching).
- Power supply board and enclosure.

**\*Note:** When unit is powered by battery back up (AC Fail condition) the voltage range is 9.3V-13.2V and 19.55V-26.4V for 12 and 24 volt operation respectively.

### **Agency Approvals**



UL Listed for Access Control System Units (UL 294).



CUL Listed - CSA Standard C22.2 No.1-98, Audio, Video and Similar Equipment.



Approved NYC Department of Buildings Approved.

## **Enclosure Dimensions**

8.5"H x 7.5"W x 3.5"D

