



# AL175ULX Multi-Output Power Supply Chargers w/Fire Alarm Interface

Rev. DSAL175ULX\_G11K



AL175ULX

## Overview

These Altronix power limited power supply/chargers that will convert 115VAC / 60Hz input, into two individually PTC protected 12VDC or 24VDC output, (see specifications).

## Specifications

- 12VDC or 24VDC selectable output.
- 1.75 amp continuous supply current.
- Class 2 Rated power limited outputs.
- Filtered and electronically regulated output.
- Short circuit and thermal overload protection.
- Maximum charge current: 400mA.
- Aux relay output (form “C” contacts).
- Automatic switch over to stand-by battery when AC fails.
- AC fail supervision (form “C” contacts).
- AC input and DC output LED indicators.

### **AL175ULX weights (approximate):**

Product weight: 8.4 lbs.  
Shipping weight: 9.4 lbs.

## Agency Approvals



UL Listed for Access Control System Units (UL 294).



CUL Listed - CSA Standard C22.2 No.205-M1983, Signal Equipment.



Approved

NYC Department of Buildings Approved.



California State Fire Marshal Approved.

# Enclosure Dimensions

13.5"H x 13"W x 3.25"D

