

**Overview**

- These multi-agency approved single output power supply/chargers convert a 115VAC/60Hz input into one (1) Class 2 Rated 12VDC or 24VDC power limited outputs.

AL300ULX

- Grey enclosure.

AL300ULXR

- Red enclosure.

Specifications

- 12VDC or 24VDC selectable output.
- 2.5 amp supply current.
- Class 2 Rated power limited output.
- Input 115VAC / 60Hz, 1.45 amp.
- Input fuse rated @ 3.5 amp/250V.
- Filtered and electronically regulated output.
- Short circuit and thermal overload protection.
- Built-in charger for sealed lead acid or gel type batteries.
- Maximum charge current .7 amp.
- Automatic switch over to stand-by battery when AC fails (zero voltage drop).
- AC fail supervision (form "C" contacts).
- Low battery supervision (form "C" contacts).
- Battery presence supervision (form "C" contacts).
- AC input and DC output LED indicators.
- Enclosure:
 - Combination knockouts are 1/2" and 3/4"
 - Accommodates up to two (2) 12VDC/7AH batteries.
- Product weight:
 - AL300ULX: 7.7 lbs.
 - AL300ULXR: 7.3 lbs.
- Shipping weight:
 - AL300ULX: 8.7 lbs.
 - AL300ULXR: 8.3 lbs.

Agency Approvals

- UL 294 UL Listed for Access Control System Units.
- UL 603 UL Listed Standard for Power Supplies for Use with Burglar-Alarm Systems.
- UL 1069 UL Listed Hospital Signaling and Nurse Call Equipment.
- UL 1481 UL Listed Standard for Safety for Fire Protective Signaling Systems.



- CUL Listed - CSA Standard C22.2 No.205-M1983, Signal Equipment.



- MEA - NYC Department of Buildings Approved.



- CSFM - California State Fire Marshal Approved.

Enclosure Dimensions
13.5"H x 13"W x 3.25"D

