

## **Overview**

This unit converts a 115VAC 60Hz input, to 12VDC @ 4 amp or 24VDC @ 3 amp of continuous supply current Class 2 Rated power limited output.

## **Specifications**

- 12VDC or 24VDC selectable output.
- 12VDC @ 4 amp or 24VDC @ 3 amp supply current.
- Class 2 Rated power limited output.
- Input 115VAC / 60Hz, 1.45 amp.
- Input fuse rated @ 3.5 amp/250V.
- Filtered and electronically regulated output.
- Short circuit and thermal overload protection.
- · Built-in charger for sealed lead acid or gel type batteries.
- Maximum charge current 0.7 amp.

- Automatic switch over to stand-by battery when AC fails (zero voltage drop).
- AC fail supervision (form "C" contacts).
- Low battery supervision (form "C" contacts).
- Battery presence supervision (form "C" contacts).
- AC input and DC output LED indicators.
- Enclosure:
  - Combination knockouts are 1/2" and 3/4"

**AL400UL weights** (approximate):

Product weight: 10.2 lbs. Shipping weight: 12.2 lbs.

## **Agency Approvals**



UL 294 **UL Listed for Access Control** System Units.

UL 603 UL Listed Standard for Power

Supplies for Use with Burglar-

Alarm Systems.

UL 1069 UL Listed Hospital Signaling and

Nurse Call Equipment.

UL 1481 UL Listed Standard for Safety for

Fire Protective Signaling Systems.

MEA Approved

MEA - NYC Department of Buildings Approved.



CSFM - California State Fire Marshal Approved.

## **Enclosure Dimensions** 12.25"H x 7.75"W x 4.5"D

