



AL600ULPD8 **Multi-Output Power Supply/Charger**

Rev. DSAL600ULPD8_A26K



Overview

This multi-agency approved multi-output power supply/chargers convert a 115VAC/60Hz input to eight (8) 12VDC or 24VDC outputs.

Specifications

- | | |
|--|---|
| <ul style="list-style-type: none">• Fuses are rated @ 3.5 amp/250V• 12VDC or 24VDC selectable outputs.• 6 amp supply current.• Eight (8) protected outputs.• Input 115VAC / 60Hz, 1.9 amp.• Input fuse rated @ 3.5 amp/250V.• Filtered and electronically regulated outputs.• Short circuit and thermal overload protection.• Built-in charger for sealed lead acid or gel type batteries.• Maximum charge current .7 amp.• Automatic switch over to stand-by battery when AC fails (zero voltage drop).• AC fail supervision (form “C” contacts).• Low battery supervision (form “C” contacts). | <ul style="list-style-type: none">• Battery presence supervision (form “C” contacts).• AC input and DC output LED indicators.• Enclosure:<ul style="list-style-type: none">- Combination knockouts are 1/2” and 3/4”- Accommodates up to two (2) 12VDC/7AH batteries.• Product weight:<ul style="list-style-type: none">- AL600ULPD8: 7.8 lbs.• Shipping weight:<ul style="list-style-type: none">- AL600ULPD8: 8.8 lbs. |
|--|---|

Agency Approvals



UL 294 UL Listed for Access Control System Units.

UL 1481 UL Listed Standard for Safety for Fire Protective Signaling Systems.



CUL Listed - CSA Standard C22.2 No.205-M1983, Signal Equipment.

Enclosure Dimensions

13.5"H x 13"W x 3.25"D

