



AL600ULPD8CB **Multi-Output Power Supply/Charger**

Rev. DSAL600ULPD8CB_G12K



AL600ULPD8CB

Overview

This multi-agency approved multi-output power supply/charger converts a 115VAC/60Hz input to eight (8) 12VDC or 24VDC outputs.

Specifications

- PTCs are rated @ 3.5 amp/250V
 - 12VDC or 24VDC selectable outputs.
 - 6 amp supply current.
 - Eight (8) PTC protected outputs.
 - Input 115VAC / 60Hz, 1.9 amp.
 - Input fuse rated @ 3.5 amp/250V.
 - Filtered and electronically regulated outputs.
 - Short circuit and thermal overload protection.
 - Built-in charger for sealed lead acid or gel type batteries.
 - Maximum charge current 0.7 amp.
 - Automatic switch over to stand-by battery when
- AC fails (zero voltage drop).
 - AC fail supervision (form “C” contacts).
 - Low battery supervision (form “C” contacts).
 - Battery presence supervision (form “C” contacts).
 - AC input and DC output LED indicators.
 - Enclosure:
 - Combination knockouts are 1/2” and 3/4”
 - Accommodates up to two (2) 12VDC/7AH batteries.

AL600ULPD8CB weights (approximate):

Product weight: 8.7 lbs.

Shipping weight: 9.6 lbs.

Agency Approvals



UL 294 UL Listed for Access Control System Units.

UL 1481 UL Listed Standard for Safety for Fire Protective Signaling Systems.



CUL Listed - CSA Standard C22.2 No.205-M1983, Signal Equipment.

Enclosure Dimensions

13.5"H x 13"W x 3.25"D

