



ALTV1224C

Overview

This Altronix ALTV1224C AC/DC Dual Output Power Supply is designed to provide both 12VDC and 24VAC outputs where a combination of both AC and DC outputs are required.

Specifications***Input:***

- 115VAC 50/60 Hz, 1.52 amp.

Output:

- Sixteen (16) individually fused outputs.
 - Eight (8) fuse protected outputs @ 12VDC.
 - Eight (8) fuse protected outputs @ 24VAC.
- 7 amp total output current.
 - 3.5 amp supply current @ 12VDC.
 - 3.5 amp supply current @ 24VAC.
- Output fuses are rated @ 3.5 amp/250VAC.
- Main fuses are rated at 5 amp/250VAC.
- Filtered and electronically regulated outputs (DC outputs).
- Surge suppression (AC outputs).

Visual Indicators:

- AC/DC power LED indicator.

Features:

- Power ON/OFF switch.
- Spare fuses provided.
- Unit maintains camera synchronization.
- Ease of installation saves time and eliminates costly labor.
- Power supply, enclosure, transformer and cam lock.
- Operating temperature: -20° C to 49° C ambient.
- BTU/Hr.:
 - 12VDC: 16 BTU/Hr.
 - 24VAC: 32 BTU/Hr.
- Product weight (approx.): 17.75 lbs. (8.05 kg.)
- Shipping weight (approx.): 19.05 lbs. (8.64 kg.)

Enclosure Dimensions (H x W x D) (approximate):
15.5" (393.7mm) x 12" (304.8mm) x 4.5" (114.3mm)

