
Overview

R1224DC16CB

The R1224DC16CB Altronix Rack Mount Power Supply provides 12VDC or 24VDC distributed via sixteen (16) PTC protected Class 2 Rated outputs for power limited installation.

Specifications***Input:***

- 115VAC 60 Hz,
3.74 amp @ 12VDC or 6.26 amp @ 24VDC.

Output:

- 12VDC @ 4.5 amp per channel of 4 outputs or 24VDC @ 4.5 amp per channel of 4 outputs. (2 amp max. per individual output).
- 18 amp total supply current.
- Sixteen (16) Class 2 Rated PTC protected power limited outputs.
- Filtered and electronically regulated outputs.
- Short circuit and thermal overload protection.

Visual Indicators:

- Power LED indicators per group of 4 outputs.

Special Features:

- Illuminated power disconnect circuit breaker with manual reset.
- Removable terminal blocks w/locking screw flange.
- IEC 320 - 3-wire grounded line cord (detachable).
- 3U rack mount chassis for use in standard EIA 19" rack.
- Ease of installation saves time and eliminates costly labor.

Enclosure:

- Enclosure dimensions: 5.21"H x 19"W x 8.5"D

R1224DC16CBweight (approximate):

Product weight: 15.7 lbs.

Shipping weight: 17.3 lbs.

Agency Approvals

Specialty Power Supply UL1012
CUL Listed - CSA Standard C22.2 No.107.1

Enclosure Dimensions (approximate)

5.21”H x 19”W x 8.5”D

