



R248UL AC Rack Mount CCTV Power Supply

Rev. DSR248UL_12082011



R248UL

Overview

This Altronix AC Rack Mount CCTV Power Supply provides 24VAC or 28VAC distributed via eight (8) fuse protected outputs for powering CCTV Cameras, heaters and other video accessories.

Specifications

Input:

- 115VAC, 50/60Hz, 0.85 amp.

Output:

- Eight (8) fuse protected outputs.
- 24VAC @ 3.5 amp (85VA) supply current
(0.4375 amp per device, 3.5 amp max.)
- or 28VAC @ 3 amp (85VA) supply current
(0.375 amp per device, 3.5 amp max.).
- Outputs are rated @ 3.5 amp.
- Surge suppression.

Electrical:

- Operating temperature: 0° C to 49° C ambient.
- 32 BTU/Hr.
- System AC input VA requirement: 97.75VA.

Mechanical:

- 2U rack mount chassis for use in standard EIA 19" rack.
- Enclosure Dimensions (H x W x D approx.):
3.26" (83mm) x 19.125" (486mm) x 8.5" (216mm)
- Product weight (approx.): 11.8 lbs. (5.35 kg.).
- Shipping weight (approx.): 12.8 lbs. (5.81 kg.).

Features:

- Eight (8) power LEDs.
- Illuminated master power disconnect circuit breaker with manual reset.
- 3-wire grounded line cord.
- Removable terminal blocks with locking screw flange.
- Spare fuses provided.

Agency Approvals



UL Listed for Commercial CCTV Equipment
(UL 2044).



CUL Listed - CSA Standard C22.2 No.1-98,
Audio, Video and Similar Equipment.



European Conformity

Enclosure Dimensions (H x W x D) (approximate):
3.26" (83mm) x 19.125" (486mm) x 8.5" (216mm)

