



R248ULCBi **Isolated Rack Mount CCTV Power Supply**

Rev. DSR248ULCBi_12132011



R248ULCBi

Overview

This Altronix Isolated Rack Mount CCTV Power Supply provides 24VAC distributed via eight (8) isolated PTC protected outputs for powering CCTV Cameras, heaters and other video accessories.

Specifications

Input:

- 115VAC, 50/60Hz, 2.7 amp.

Output:

- Eight (8) isolated PTC protected outputs.
- 24VAC @ 12.5 amp (300VA) supply current
(1.56 amp per device, 3.5 amp max.)
- Outputs are rated @ 2.5 amp.
- Surge suppression.

Electrical:

- Operating temperature: 0° C to 49° C ambient.
- 114 BTU/Hr.
- System AC input VA requirement: 310.5VA.

Mechanical:

- 2U rack mount chassis for use in standard EIA 19" rack.
- Enclosure Dimensions (H x W x D approx.):
3.26" (83mm) x 19.125" (486mm) x 8.5" (216mm)
- Product weight (approx.): 17.2 lbs. (7.80 kg.).
- Shipping weight (approx.): 18.2 lbs. (8.26 kg.).

Features:

- Eight (8) power LEDs.
- Illuminated master power disconnect circuit breaker with manual reset.
- 3-wire grounded line cord.
- Removable terminal blocks with locking screw flange.
- Spare fuses provided.

Agency Approvals



UL Listed for Commercial CCTV Equipment
(UL 2044).



CUL Listed - CSA Standard C22.2 No.1-98,
Audio, Video and Similar Equipment.



European Conformity

Enclosure Dimensions (H x W x D) (approximate):
3.26" (83mm) x 19.125" (486mm) x 8.5" (216mm)

