



R615DC616UL **DC Rack Mount CCTV Power Supply**

Rev. R615DC616UL_12062011

Overview



R615DC616UL

This Altronix DC Rack Mount CCTV Power Supply provides 6-15VDC distributed via sixteen (16) fuse protected outputs for powering CCTV cameras, heaters and other video accessories.

Specifications

Input:

- 115VAC, 50/60Hz, 1.5 amp.

Output:

- Sixteen (16) fuse protected outputs.
- 6-15VDC @ 6 amp total output current.
(0.375 amp per device, 3.5 amp max.)
- Outputs are rated @ 3.5 amp.
- Filtered and electronically regulated outputs.
- Short circuit and thermal overload protection.

Electrical:

- Operating temperature: 0° C to 49° C ambient.
- Total system power consumption: 90 W.
- 14-34 BTU/Hr.
- System AC input VA requirement: 90VA.

Mechanical:

- 2U rack mount chassis for use in standard EIA 19" rack.
- Enclosure Dimensions (H x W x D approx.): 3.26" (83mm) x 19.125" (486mm) x 8.5" (216mm)
- Product weight (approx.): 17.15 lbs. (7.78 kg.).
- Shipping weight (approx.): 18.15 lbs. (8.23 kg.).

Features:

- Sixteen (16) power LEDs.
- Illuminated master power disconnect circuit breaker with manual reset.
- 3-wire grounded line cord.
- Removable terminal blocks with locking screw flange.
- Spare fuses provided.

Agency Approvals



UL Listed for Commercial CCTV Equipment
(UL 2044).



CUL Listed - CSA Standard C22.2 No.1-98,
Audio, Video and Similar Equipment.

Enclosure Dimensions (H x W x D) (approximate):
3.26" (83mm) x 19.125" (486mm) x 8.5" (216mm)

