



R615DC616ULCB **DC Rack Mount CCTV Power Supply**

Rev. R615DC616ULCB_12062011

Overview



R615DC616ULCB

This Altronix DC Rack Mount CCTV Power Supply provides 6-15VDC distributed via sixteen (16) PTC protected outputs for powering CCTV cameras, heaters and other video accessories.

Specifications

Input:

- 115VAC, 50/60Hz, 1.5 amp.

Output:

- 6-15VDC @ 6 amp total output current.
- Sixteen (16) PTC protected outputs.
- Outputs are rated @ 2.5 amp.
- Filtered and electronically regulated outputs.
- Short circuit and thermal overload protection.

Visual Indicators:

- DC power LED indicators.

Features:

- Illuminated master power switch with built-in circuit breaker.

Features (cont'd):

- 3-wire grounded line cord.
- Removable terminal blocks with locking screw flange.
- Spare fuses provided.
- Unit maintains camera synchronization.
- Ease of installation saves time and eliminates costly labor.
- 2U rack mount chassis for use in standard EIA 19" rack.
- Operating temperature: 0° C to 49° C ambient.
- 14-34 BTU/Hr.
- Product weight (approx.): 17.15 lbs. (7.78 kg.)
- Shipping weight (approx.): 18.15 lbs. (8.23 kg.)

Agency Approvals



UL Listed for Commercial CCTV Equipment (UL 2044).



CUL Listed - CSA Standard C22.2 No.1-98, Audio, Video and Similar Equipment.

Enclosure Dimensions (H x W x D) (approximate):
3.26" (83mm) x 19.125" (486mm) x 8.5" (216mm)

