



R615DC8UL **DC Rack Mount CCTV Power Supply**

Rev. R615DC8UL_12062011

Overview



R615DC8UL

This Altronix DC Rack Mount CCTV Power Supply provides 6-15VDC distributed via eight (8) fuse protected outputs for powering CCTV cameras, heaters and other video accessories.

Specifications

Input:

- 115VAC, 50/60Hz, 0.9 amp.

Output:

- Eight (8) fuse protected outputs.
- 6-15VDC @ 4 amp total output current.
(0.5 amp per device, 3.5 amp max.)
- Outputs are rated @ 3.5 amp.
- Filtered and electronically regulated outputs.
- Short circuit and thermal overload protection.

Electrical:

- Operating temperature: 0° C to 49° C ambient.
- Total system power consumption: 60 W.
- 9-23 BTU/Hr.
- System AC input VA requirement: 60VA.

Mechanical:

- 2U rack mount chassis for use in standard EIA 19" rack.
- Enclosure Dimensions (H x W x D approx.): 3.26" (83mm) x 19.125" (486mm) x 8.5" (216mm)
- Product weight (approx.): 12.4 lbs. (6.19 kg.).
- Shipping weight (approx.): 13.4 lbs. (6.65 kg.).

Features:

- Eight (8) power LEDs.
- Illuminated master power disconnect circuit breaker with manual reset.
- 3-wire grounded line cord.
- Removable terminal blocks with locking screw flange.
- Spare fuses provided.

Agency Approvals



UL Listed for Commercial CCTV Equipment (UL 2044).



CUL Listed - CSA Standard C22.2 No.1-98, Audio, Video and Similar Equipment.

Enclosure Dimensions (H x W x D) (approximate):
3.26" (83mm) x 19.125" (486mm) x 8.5" (216mm)

