

### **Overview**



Sav36D

Altronix Sav36D Power Supply provides 12VDC distributed via thirty-six (36) Class 2 Rated PTC protected power limited outputs for powering surveillance cameras.



### **Specifications**

**Input:**

- 115VAC 60Hz, 3 amp /230VAC 50Hz, 1.5 amp.

**Output:**

- 12VDC @ 11 amp total output current (0.30 amp per device, 2.5 amp max.).
- Thirty-six (36) Class 2 Rated PTC protected power limited outputs.
- Filtered and electronically regulated outputs.
- Short circuit and thermal overload protection.

**Electrical:**

- Operating temperature: 0° C to 49° C ambient.
- Total system power consumption: 132 W.
- 50 BTU/Hr.
- System AC input VA requirement: 345VA.

**Mechanical:**

- NEMA1 enclosure.
- Enclosure Dimensions (H x W x D approx.): 13.5" (342.9mm) x 13" (330.2mm) x 3.25" (82.55mm)
- Product weight (approx.): 7.75 lbs. (3.52 kg.).
- Shipping weight (approx.): 8.25 lbs. (3.74 kg.).

**Features:**

- Thirty-six (36) power LEDs.
- Power ON/OFF switch.
- Field installable 3-wire line cord with integral strain relief.
- Unit maintains camera synchronization.
- Ease of installation saves time & eliminates costly labor.

### **Agency Approvals**



UL Listed for Commercial CCTV Equipment (UL 2044).



CUL Listed - CSA Standard C22.2 No.1-98, Audio, Video and Similar Equipment.

**Enclosure Dimensions (H x W x D) (approximate):**

13.5" (342.9mm) x 13" (330.2mm) x 3.25" (82.55mm)

