



T2428100C

Overview

This AC power supply provides power for electronic power supplies and equipment including security, access control and surveillance devices.

Specifications

Input:

- 115VAC 50/60 Hz, 0.95 amp.

Output:

- 24VAC @ 4 amp @ 28VAC @ 3.5 amp supply current.

Features:

- Fused input protection.
- Green grounding lead.

Electrical:

- Operating temperature: -20°C to 49°C ambient.
- 38 BTU/Hr.

Mechanical:

- Product weight (approx.): 5.0 lbs. (2.27 kg.).
- Shipping weight (approx.): 5.7 lbs. (2.59 kg.).

Enclosure Dimensions (H x W x D) (approximate):

5.5" (139.7mm) x 7" (177.8mm) x 4.45" (113.03mm)

