



T2428300E

Overview

This AC power supply provides power for equipment including security, access control and surveillance devices.

Specifications

Input:

- 115VAC 50/60 Hz, 2.7 amp.

Output:

- 24VAC @ 14 amp or
- 28VAC @ 12.5 amp supply current.

Electrical:

- Operating temperature: -20° C to 49° C ambient.
- BTU/Hr.:
 - 24VAC: 114 BTU/Hr.
 - 28VAC: 106 BTU/Hr.

Mechanical:

- Product weight (approx.): 7.2 lbs. (3.27 kg.).
- Shipping weight (approx.): 8.5 lbs. (3.86 kg.).

Enclosure Dimensions (H x W x D) (approximate)

12.25" (311.15mm) x 7.5" (190.5mm) x 4.5" (114.3mm)

