



TP1640

Overview

TP1640 transformer provides 16.5VAC with a total of 1.2 amp output current.

Specifications***Input:***

- 115VAC 50/60 Hz, 0.48 amp.

Output:

- 16.5VAC/40VA (2.4 amp) output.

Electrical:

- Operating temperature: 0° C to 49° C ambient.

Electrical (cont'd):

- 15 BTU/Hr.
- System AC input VA requirement: 55.2VA.

Mechanical:

- Dimensions (H x W x D approx.):
3.562" (90.47mm) x 2.658" (67.51mm)
x 2.353" (59.77mm)
- Product weight (approx.): 1.25 lbs. (0.57 kg.).
- Shipping weight (approx.): 1.55 lbs. (0.70 kg.).

Plug-in Transformer Diagram