

---

**Overview**

VertiLine33D

**VERTILINE™**

Altronix Vertiline33D Rack Mount DC Power Supply provides sixteen (16) filtered and electronically regulated power outputs in a space saving 1U EIA 19" rack mount chassis. This unit is available with 12VDC power outputs. Vertiline Rack Mount DC Power Supplies are also available in eight (8) outputs.

---

**Specifications*****Input:***

- 115VAC 60 Hz, 1.5 amp input.

***Output:***

- 12VDC outputs rated @ 8 amp total current max. (0.5 amp per device, 2.5 amp max.).
- Sixteen (16) PTC protected power outputs.
- Filtered and electronically regulated.

***Electrical:***

- Operating temperature: -20° C to 49° C ambient.
- Total system power consumption: 100 W.
- 36 BTU/Hr.
- System AC input VA requirement: 100VA.

***Mechanical:***

- Units can be rack, wall or shelf mounted.

***Mechanical (cont'd):***

- Modular 1U standard EIA 19" rack mount chassis
- Enclosure Dimensions (H x W x D approx.): 1.625" (41.275mm) x 19.125" (486mm) x 8.5" (216mm)
- Product weight (approx.): 8.15 lbs. (3.7 kg.).
- Shipping weight (approx.): 9.45 lbs. (4.29 kg.).

***Features:***

- Sixteen (16) power LEDs.
- Illuminated master power disconnect circuit breaker with manual reset.
- IEC 320 - 3-wire grounded line cord (detachable).
- Removable terminal blocks with locking screw flange.

---

**Agency Approvals**

European Conformity

***Enclosure Dimensions (H x W x D) (approximate):***  
**1.625" (41.275mm) x 19.125" (486mm) x 8.5" (216mm)**

