
Overview

VertiLine63TD

VERTILINE™

Altronix Vertiline63TD Rack Mount DC Power Supply provides sixteen (16) filtered and electronically regulated power outputs in a space saving 1U EIA 19" rack mount chassis. This unit is available with 24VDC power outputs.

Vertiline Rack Mount Power Supplies are also available in eight (8) outputs.

Specifications***Input:***

- 115VAC 60 Hz, 6 amp input.

Output:

- 24VDC outputs rated @ 16 amp total current max. (1.0 amp per device, 2.5 amp max.).
- Sixteen (16) PTC protected power outputs.
- Filtered and electronically regulated.

Electrical:

- Operating temperature: -20° C to 49° C ambient.
- Total system power consumption: 385 W.
- 146 BTU/Hr.
- System AC input VA requirement: 385VA.

Mechanical:

- Units can be rack, wall or shelf mounted.

Mechanical (cont'd):

- Modular 1U standard EIA 19" rack mount chassis
- Enclosure Dimensions (H x W x D approx.): 1.625" (41.275mm) x 19.125" (486mm) x 8.5" (216mm)
- Product weight (approx.): 9.3 lbs. (4.22 kg.).
- Shipping weight (approx.): 10.6 lbs. (4.81 kg.).

Features:

- Sixteen (16) power LEDs.
- Illuminated master power disconnect circuit breaker with manual reset.
- IEC 320 - 3-wire grounded line cord (detachable).
- Removable terminal blocks with locking screw flange.

Agency Approvals

European Conformity

Enclosure Dimensions (H x W x D) (approximate):
1.625" (41.275mm) x 19.125" (486mm) x 8.5" (216mm)

