

Overview



VertiLine6D

VERTILINE™

Altronix Vertiline6D Rack Mount DC Power Supply provides eight (8) filtered and electronically regulated power outputs in a space saving 1U EIA 19" rack mount chassis.

This unit is available with 12VDC power outputs. Vertiline Rack Mount DC Power Supplies are also available in sixteen (16) outputs.

Specifications

Input:

- 115VAC 60 Hz, 3 amp input.

Output:

- 24VDC outputs rated @ 8 amp total current max. (1.0 amp per device, 2.5 amp max.).
- Eight (8) PTC protected power outputs.
- Filtered and electronically regulated.

Electrical:

- Operating temperature: -20° C to 49° C ambient.
- Total system power consumption: 200 W.
- 73 BTU/Hr.
- System AC input VA requirement: 200VA.

Mechanical:

- Units can be rack, wall or shelf mounted.

Mechanical (cont'd):

- Modular 1U standard EIA 19" rack mount chassis
- Enclosure Dimensions (H x W x D approx.): 1.625" (41.275mm) x 19.125" (486mm) x 8.5" (216mm)
- Product weight (approx.): 8.0 lbs. (3.63 kg.).
- Shipping weight (approx.): 9.3 lbs. (4.22 kg.).

Features:

- Eight (8) power LEDs.
- Illuminated master power disconnect circuit breaker with manual reset.
- IEC 320 - 3-wire grounded line cord (detachable).
- Removable terminal blocks with locking screw flange.

Agency Approvals



European Conformity

Enclosure Dimensions (H x W x D) (approximate):
1.625" (41.275mm) x 19.125" (486mm) x 8.5" (216mm)

