
Overview

- Converts a 24VAC or 24VDC input into a regulated 12VDC output.



Specifications

- Converts a 24VAC or 24VDC input to a 12VDC output.
 - 12VDC @ 3 amp max.
 - Power LED indicator.
 - Electronically filtered and regulated output.
 - Built-in overload protection.
 - Spring terminals.
 - High impact insulated housing.
 - Compact design allows for integration in a wide range of camera housings.
 - Screw mounting.
- Dimensions (approximate): 3.375"L x 2.5"W x 1.125"H

Applications

- Power for CCTV cameras and accessories, Fiber Optic Transmitters, REX PIR's, Prox Readers, etc.

Agency Approvals