

# Altronix® WPTV244175UL UL Listed AC Outdoor CCTV Power Supply

Rev. DSWPTV244175UL\_C16K

#### **Overview**

This Altronix outdoor CCTV Power Supply provides power via four (4) protected outputs for CCTV Cameras, heaters and other video accessories.



WPTV244175UL

#### **Specifications**

- 24VAC @ 7 amp (170VA) or 28VAC @ 6.25 amp (175VA).
- Input 115VAC 50/60 Hz.
- Four (4) protected outputs:
  - One (1) fuse protected non-power limited output.
  - Three (3) Class 2 Rated PTC protected power limited outputs rated @ 2.5 amp.
- Illuminated power disconnect circuit breaker with manual reset.
- Surge suppression.

- AC power LED.
- Spare fuses provided.
- Unit maintains camera synchronization.
- Ease of installation saves time & eliminates costly labor.
- NEMA 4 Rated enclosure for outdoor use. WPTV244175UL weights (approximate):

Product weight: 14.75 lbs.

Shipping weight: 16.0 lbs.

### Agency Approvals



UL Listed for Commercial CCTV Equipment (UL 2044).



**European Conformity** 



CUL Listed - CSA Standard C22.2 No.1-98, Audio, Video and Similar Equipment.

## **Enclosure Dimensions** 12"H x 8"W x 6"D

