



# **WPTV244300UL** **UL Listed AC Outdoor CCTV Power Supply**

Rev. DSWPTV244300UL\_C16K

## **Overview**

This Altronix outdoor CCTV Power Supply provides power via four (4) protected outputs for CCTV Cameras, heaters and other video accessories.



WPTV244300UL

## **Specifications**

- 24VAC @ 12.5 amp (300VA) or 28VAC @ 10 amp (280VA).
  - Input 115VAC 50/60 Hz.
  - Four (4) protected outputs:
    - One (1) fuse protected non-power limited output.
    - Three (3) Class 2 Rated PTC protected power limited outputs rated @ 2.5 amp.
  - Illuminated power disconnect circuit breaker with manual reset.
  - Surge suppression.
  - AC power LED.
  - Spare fuses provided.
  - Unit maintains camera synchronization.
  - Ease of installation saves time & eliminates costly labor.
  - NEMA 4 Rated enclosure for outdoor use.
- WPTV244300UL weights (approximate):***  
Product weight: 15.15 lbs.  
Shipping weight: 16.4 lbs.

## **Agency Approvals**



UL Listed for Commercial CCTV Equipment (UL 2044).



CUL Listed - CSA Standard C22.2 No.1-98, Audio, Video and Similar Equipment.



European Conformity

**Enclosure Dimensions**

12"H x 8"W x 6"D

