


ShawFlex Item #: 4D010M040300000

3C 4 /7B NS XLPE PVC 1000V CSA Tray Cable TC (Direct Burial)



Cable Parameters

Description	Abbreviations	
Type of Conductor Stranding:	C _s	4AWG 7W BARE COPPER (Concentric)
Diameter of Conductor (in):	C _d	0.225 (5.72 mm)
Insulation Type	I	FR XLPE (RW90)
Insulation Thickness (in):	I _t	0.060 (1.52 mm)
Nominal Insulated Wire Diameter (in):	I _{cd}	0.349 (8.86 mm)
Jacket Type & Color:	J	90C -40C FR PVC, BLACK
Jacket Thickness (in):	J _t	0.080 (2.03 mm)
Nominal Overall OD of Cable (in):	C _d	0.930 (23.6 mm)
Ground Wire Size:	GW _s	8AWG 7W BARE COPPER
Cable Weight (lbs/Mft):		696 (1036 kg/km)