

Product Data Sheet

RGB Coax Cable

Product Description

Mini RGB and RGBHV multi-coaxial cable for component video and control signals between video sources and receivers; such as video projectors, LCD projectors, plasma screens, televisions, white boards, etc.

Specifications

- CONDUCTOR: Solid bare copper
- SHIELDING: Foil tape + 95% tinned copper serve shield
- INSULATION: Foam-HDPE
- JACKET: Polyvinyl Chloride (PVC)
- IMPEDANCE: 75 OHM
- NEC: CMR or CL3R
- RATINGS: 75C, 300V

Part No.	Description	Nom. O.D. (in.)	Approx. Wt. lb./1,000 ft.
AV-RGB3CR	3C 25 AWG solid bare copper, red-green-blue individual mini coax, foil tape, 95% tinned copper braid, overall black PVC jacket.	0.313	43
AV-RGB5CR	5C 25 AWG solid bare copper, red-green-blue-white-yellow individual mini coax, foil tape, 95% tinned copper braid, overall black PVC jacket.	0.364	69
AV-RGB6CR	6C 25 AWG solid bare copper, red-green-blue-white-yellow-black individual mini coax, foil tape, 95% tinned copper braid, overall black PVC jacket.	0.395	80