

# Product Data Sheet

## High Pair-count Riser-rated Cables - Category 3

### Product Description

For use as a high pair-count backbone per ANSI/TIA-568-A. Near-end crosstalk (NEXT) is measured using the Power SUM (PS) method. This method accounts for all the energy present in 25-pair cable.

### Specifications

- 24 AWG
- Solid bare copper conductors
- Conductors are twisted into varying lengths of lay to minimize crosstalk
- PVC insulation
- PVC jacket

### Tech. Info & Standards

ANSI/TIA Category 3 compliant

UL Listed CMR

NOTE: Dimensions and weights vary by construction and manufacturer

Part No.	No. of Pairs	Nom. O.D. (in.)	Approx. Wt. lb./1,000 ft.
CM-02524BAG-3	25	0.355	99
CM-05024BAG-3	50	0.510	180
CM-10024BAG-3	100	0.685	345