Diagonal-Cutting Pliers

High-Leverage Diagonal-Cutting Pliers – Angled Head

Additional Features:

- Angled head design for easy work in confined spaces.
- High-leverage design. Rivet is closer to the cutting edge for 36% greater cutting and gripping power than other plier designs.
- Short jaws and beveled cutting edges permit close cutting of wire.
- Induction-hardened cutting knives for long life.
- Hot-riveted joint ensures smooth action and no handle wobble.

JOURNEYMAN



Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Cutting Knives	Handle Finish	Handle Color	Weight (lbs.)
J248-8	8-1/8" (206 mm)	13/16" (21 mm)	1-3/16" (30 mm)	7/16" (11 mm)	standard	Journeyman	red/black	.61
2000 Series* – Heavy-duty cutting knives								
J2000-48	8-1/8" (206 mm)	13/16" (21 mm)	1-3/16" (30 mm)	7/16" (11 mm)	standard	Journeyman	light blue/black	.61
*Cuto ACCD	corowe pails and most	t hardanad wira Faat	uras combination polic	shad and black avida	finich			

Long-Nose Pliers

Heavy-Duty Long-Nose Pliers – Side-Cutting

Additional Features:

- Induction-hardened, long-lasting cutting knives.
- Heavier design for greater cutting power.
- Extended handles provide added reach and leverage.
- Slim head design for working in confined areas.
- Hot-riveted joint ensures smooth action and no handle wobble.





Knife Point Length Thickness	Handle Finish	Handle Color	Weight (lbs.)
5/8" (16 mm) 1/8" (3 mm)	Journeyman	yellow/black	.63

Cat. No. **Overall Length** Jaw Width Length Thickness J203-8 8-9/16" (218 mm) 2-5/16" (59 mm) 1" (25 mm) 1/2" (13 mm) Wire Stripping - Cleanly strips 12 AWG wire J203-8N 8-9/16" (218 mm) 2-5/16" (59 mm) 1" (25 mm) 1/2" (13 mm) 5/8" (16 mm) 1/8" (3 mm) yellow/black Journeyman .64

Standard Long-Nose Pliers

JOURNEYMAN

Additional Features:

- Slim head design for working in confined areas.
- Induction-hardened, long-lasting cutting knives.
- Knurled jaws for sure wrapping and looping.
- Hot-riveted joint ensures smooth action and no handle wobble.

TM		
	389	
		J203-7

Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Point Thickness	Handle Finish	Handle Color	Weight (lbs.)
J203-6	6-3/4" (171 mm)	1-7/8" (48 mm)	11/16" (18 mm)	3/8" (10 mm)	1/2" (13 mm)	3/32" (2 mm)	Journeyman	yellow/black	.30
J203-7	7-5/16" (186 mm)	2-7/16" (62 mm)	11/16" (18 mm)	3/8" (10 mm)	1/2" (13 mm)	3/32" (2 mm)	Journeyman	yellow/black	.33

All dimensions are in inches and (millimeters)

AWARNING: Always wear approved eye protection.

AWARNING: NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock.

