



Innovative design for all-day comfort and easy on/off



Up to 120 metre wireless range

Savi® 430

DECT™ quality wireless audio for the PC

The first portable PC-based wireless headset system that incorporates DECT™ technology for unsurpassed, enterprise-grade audio quality, even in dense working environments. Hands-free functionality increases productivity by enabling users to multitask and move freely around the office.

IDEAL FOR:

- Flexible office worker using PC for voice telephony and multimedia
- Best audio quality for hectic busy offices

Savi 430

The first portable PC-based wireless headset system that incorporates DECT™ technology for unsurpassed, enterprise-grade audio quality, even in dense working environments. Hands-free functionality increases productivity by enabling users to multitask and move freely around the office.

KEY FEATURES

Outstanding sound quality

- DECT technology provides better audio; eliminates interference from Wi-Fi networks
- Advanced wideband audio using CAT-iq technology for high definition voice quality
- Noise-cancelling microphone filters out background noise
- Digital Signal Processing (DSP) provides more natural voice sound

User-friendly function and design

- DECT dongle has 180° articulation for optimal positioning and storage
- Intuitive call controls including answer/end with supported softphones
- Excellent range of up to 120 metres allows hands free productivity
- Easy magnetic headset docking
- Adaptive battery for longer talk time
- Conference up to three additional headsets for improved call efficiency

Ease of install

- Plug-and-play installation
- Optional control panel installation



ADDITIONAL INFORMATION

Connects to:	PC
Ideal for:	Users in office environments requiring the highest sound quality for PC communications and the convenience of portability
Wireless frequency:	DECT, range up to 120 metres
Hearing protection:	SoundGuard™ protects against sound levels above 118dBA
Call control compatibility:	Electronic Hookswitch cables available for Alcatel, Avaya, Cisco, Polycom, Siemens compatibility: systems or HL10™ handset lifted accessory. Softphone support via software
Headset weight:	Over-the-ear – 24 grams
Talk time:	Up to 6 hours
Modularity support:	Charger and headset disconnect from one base to subscribe to another base
Limited warranty:	2 year

BACKED BY PLANTRONICS GLOBAL SERVICE AND SUPPORT

For more information about the Savi 430 or other Plantronics products, please visit our web site at: plantronics.com

	MODEL NUMBER	PART NUMBER
Standard version	W430A	82396-12
 Optimized for Microsoft Office Communicator	W430A-M	82397-12

© 2012 Plantronics, Inc. All rights reserved. Plantronics, the logo design; Savi, SoundGuard and Sound Innovation are trademarks or registered trademarks of Plantronics, Inc. DECT is a trademark of ETSI registered for the benefit of its members in France and other jurisdictions. Microsoft is a trademark or registered trademark of Microsoft Corporation in the U.S. and other countries. Alcatel and their respective logos are trademarks and service marks of Alcatel-Lucent, Alcatel and Lucent Technologies. Siemens is a registered trademark of Siemens AG. Polycom is a trademark or registered trademark of Polycom, Inc. 06/12.

