



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: PDU1415

Single-Phase Basic PDU, 15A 120V, 0U Vertical Rackmount, 14 NEMA 5-15R outlets, NEMA 5-15P input plug

Highlights

- Basic single phase 15A 120V PDU
- 0U vertical rackmount installation
- NEMA 5-15P input; 15 ft. / 4.5m line cord
- 14 NEMA 5-15R outlets
- 24 in. / 61cm housing



Description

Tripp Lite Basic Power Distribution Units / PDU systems offer reliable rackmount power distribution. Supplies equipment with continuous power from any protected UPS, generator or mains input power source. High quality design includes rugged all-metal housing and secure rackmount installation with included mounting accessories.

Applications

- Multi-outlet power distribution unit is the ideal means of powering multiple loads in racks, wallmount and other applications, such as internetworking, PC systems, telecommunications, audio/video, security, sound reinforcement and more. Ideal for distribution of UPS, generator or commercially derived AC power to protected equipment.

Package Includes

- PDU1415
- Instruction manual with warranty information

Features

- 15A single phase 120V Basic Power Distribution Unit / PDU
- Attached NEMA 5-15P 15A 120V input plug with 15 ft. / 4.5m line cord
- 0U, 24 in / 61cm vertical form factor supports installation in 2 or 4 post equipment racks
- Toolless mounting supported in button-mount compatible racks, plus nut-and-bolt mounting brackets for other mounting applications

Specifications

OVERVIEW	
PDU Type	Basic
OUTPUT	
Frequency compatibility	50 / 60 Hz
Output watts	1800
Output nominal voltage	120V
Overload protection	15A

Outlet quantity / type	14 NEMA 5-15R
Outlet Type	NEMA 5-15R
INPUT	
Nominal Input Voltage(s) Supported	120V AC
PDU Input Voltage	100; 120; 127
Maximum Input Amps (A)	15
PDU Plug Type	NEMA 5-15P
Input cord length (ft.)	15
Input cord length (m)	4.57
Voltage compatibility (VAC)	120
Phase	Single-Phase
LEDS ALARMS & SWITCHES	
Switches	No switch
PHYSICAL	
Shipping weight (lbs)	5.2
Shipping weight (kg)	2.4
Unit Dimensions (HWD/in)	1.75 x 25.75 x 2.25
Unit Dimensions (HWD/cm)	4.45 x 65.4 x 5.7
Shipping Dimensions (HWD/in)	2.75 x 27.25 x 8.25
Shipping Dimensions (HWD/cm)	7 x 69.2 x 21
Unit weight (lbs)	4.6
Unit weight (kg)	2.1
Material of construction	Steel
Style	Rackmount, Vertical Rackmount, Wallmount/Under-Counter
Form factors supported	Vertical or horizontal mounting supported in wallmount applications, racks and a variety of other surface types
PDU Form Factor	Vertical (0U)
CERTIFICATIONS	
Certifications	Tested to UL60950-1 (USA) and CAN/CSA C22.2 No. 60950-1-03 (Canada)
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

Related Items

Optional Products

Related Model	Description	Qty.
P006-006-13LA	6-ft. 18AWG Power cord (NEMA 5-15P to IEC-320-C13 Left Angle)	1
P006-006-13RA	6-ft. 18AWG Power cord (NEMA 5-15P to IEC-320-C13 Right Angle)	1
P022-001	1-ft. 18AWG Power Extension cord (NEMA 5-15R to NEMA 5-15P)	1
P023-001	1-ft. 14AWG Power Adapter cord (NEMA L5-15R to NEMA 5-15P)	1
P007-002	2-ft. Heavy-Duty 14AWG Power cord (IEC-320-C13 to NEMA 5-15P)	1
P030-002-5	5-Pack of 2-ft. 18AWG Power Cords NEMA 5-15P to IEC-320-C13)	1
P006-003	3-ft. 18AWG Power cord (NEMA 5-15P to IEC-320-C13)	1
P006-004	4-ft. 18AWG Power cord (NEMA 5-15P to IEC-320-C13)	1
P006-004-BL	4-ft. 18AWG Power Cord (NEMA 5-15P to IEC-320-C13) with Blue Connectors	1
P006-004-GN	4-ft. 18AWG Power Cord (NEMA 5-15P to IEC-320-C13) with Green Connectors	1
P006-004-RD	4-ft. 18AWG Power Cord (NEMA 5-15P to IEC-320-C13) with Red Connectors	1
P006-004-YW	4-ft. 18AWG Power Cord (NEMA 5-15P to IEC-320-C13) with Yellow Connectors	1
P006-006	6-ft. 18AWG Power cord (NEMA 5-15P to IEC-320-C13)	1
P006-006-2	6-ft. AC Power Splitter Cable (NEMA 5-15P to 2 x IEC-320-C13)	1
P006-006-515MF	6 ft. Piggyback Power Cord (NEMA 5-15P/R to IEC-320-C13)	1
P007-006	6-ft. Heavy-Duty 14AWG Power cord (IEC-320-C13 to NEMA 5-15P)	1
P007-010	10-ft. Heavy-Duty 14AWG Power cord (IEC-320-C13 to NEMA 5-15P)	1
P034-010	10-ft. 14AWG Heavy Duty Power cord (IEC-320-C19 to NEMA 5-15P)	1
P006-010	10-ft. 18AWG Power cord (NEMA 5-15P to IEC-320-C13)	1
P010-012	12-ft. 18AWG Power cord (NEMA 5-15P to IEC-320-C13)	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=2952.

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.