



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: PS-415-HG

NOT For Patient Areas - 4-outlet Power Strip with Hospital-Grade Plug & Receptacles



Highlights

- Versatile power distribution strip
- 4 hospital-grade receptacles and hospital-grade plug
- 15-ft. cord
- 15A resettable circuit breaker

Description

Tripp Lite's PS-415-HG Power Strip offers 15A AC power distribution in a rugged all-metal outlet strip for 120V applications. Features 4 output receptacles, 15-ft. AC power cord and a built-in resettable circuit breaker that controls power to all outlets and protects against overloads. Switchless design prevents accidental shutoff. Optional-use keyhole mounting tabs and flanges.

PLUG/OUTLETS: NEMA 5-15P-HG hospital-grade plug and 4 NEMA5-15R-HG hospital-grade receptacles

ELECTRICAL: 120V AC, 50/60Hz, 15A

FORMAT: All-metal corded multi-outlet strip

Applications

- AC power distribution with hospital-grade receptacles and plug where durability and reliability are required.
- Not for use where NEC requires hospital-grade receptacles.

Package Includes

- PS-415-HG Power Strip
- Owner's manual and warranty information

Features

- Rugged all-metal housing withstands years of use without breakage
- 4 x NEMA 5-15R-HG hospital-grade output receptacles
- 15-ft. AC cord with integrated, molded NEMA5-15P-HG hospital-grade plug
- Optional-use keyhole mounting tabs and flanges
- Switchless design prevents accidental shutoff
- 15A electrical capacity with built-in resettable circuit breaker
- 120V, 50/60Hz
- Certified by UL (USA) and cUL (Canada)

Specifications

OVERVIEW	
Model Type	NOT For Patient Areas
OUTPUT	
Frequency compatibility	50 / 60 Hz
Circuit Breaker (amps)	15
Overload protection	15A circuit breaker
Outlet quantity / type	4 NEMA 5-15R-HG
Outlet orientation	Single row of 4
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input connection type	NEMA 5-15P-HG
Input cord length (ft.)	15
Input cord length (m)	4.572
Voltage compatibility (VAC)	120
LEDS ALARMS & SWITCHES	
Alarms	No power switch
PHYSICAL	
Unit Dimensions (HWD/in)	1.5 x 8.65 x 2.5
Unit Dimensions (HWD/cm)	3.8 x 21.9 x 6.4
Material of construction	Metal
Integrated keyhole mounting tabs	Keyhole mounting tabs and flanges enable mounting to a variety of surfaces
Receptacle Color	White
AC line cord color	White
Outlets center to center measurement	Inner outlets = 32.5mm
Keyhole slot center to center measurement	Distance between keyhole tabs = 127mm; Distance between end tabs = 207.45mm
CERTIFICATIONS	
UL1363 (Power Tap)	UL1363 (Series Number: AGIB12015SL)
cUL / CSA (Canada)	cUL (Series Number: AGIB12015SL)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=2561.

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.