



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: PS-606-HG

### NOT For Patient Areas - 6-outlet Power Strip with Hospital-Grade Plug & Receptacles & 6-ft. Cord



#### Highlights

- Versatile power distribution strip
- 6 hospital-grade outlets and hospital-grade plug
- 6-ft. cord
- 15A resettable circuit breaker
- UL, cUL approved

#### Description

Tripp Lite's PS-606-HG power strip offers 15A capacity AC power distribution in a rugged, all-metal outlet strip for 120V applications. Features 6 hospital-grade receptacles, 6-ft. power cord and built-in 15A resettable circuit breaker. Switchless design prevents accidental shutoff. Optional use keyhole mounting tabs and flanges.

PLUG/OUTLETS: NEMA 5-15P-HG hospital-grade plug and 6 NEMA 5-15R-HG hospital-grade receptacles

ELECTRICAL: 120V AC, 50/60 Hz, 15A

FORMAT: all-metal corded multi outlet strip

#### Applications

- AC power distribution with hospital-grade receptacles and plug where durability and reliability are required.
- Not for use where NEC requires hospital-grade receptacles.

#### Package Includes

- PS-606-HG Power Strip
- User manual with warranty information

#### Features

- Rugged all-metal housing withstands years of use without breakage
- 6 x NEMA 5-15R-HG hospital-grade receptacles
- 6-ft. AC cord with integrated, molded NEMA 5-15P-HG hospital-grade plug
- Optional-use keyhole mounting tabs and flanges
- Switchless design prevents accidental shutoff
- 15A electrical capacity with built-in resettable circuit breaker
- 120V, 50/60 Hz electrical compatibility
- Certified by UL (USA) and cUL (Canada)

#### Specifications

---

<b>OVERVIEW</b>	
Model Type	NOT For Patient Areas
<b>OUTPUT</b>	
Frequency compatibility	50 / 60 Hz
Circuit Breaker (amps)	15
Overload protection	15A circuit breaker
Outlet quantity / type	6 NEMA 5-15R-HG
Outlet orientation	Single row of 6
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A, 120V
Input connection type	NEMA 5-15P-HG
Input cord length (ft.)	6
Input cord length (m)	1.83
Voltage compatibility (VAC)	120
<b>LEDS ALARMS &amp; SWITCHES</b>	
Switches	No power switch
<b>PHYSICAL</b>	
Shipping weight (lbs)	3.5
Shipping weight (kg)	1.6
Unit Dimensions (HWD/in)	1.5 x 13.75 x 2.5
Unit Dimensions (HWD/cm)	3.8 x 34.9 x 6.4
Unit weight (lbs)	2.4
Unit weight (kg)	1.1
Material of construction	Metal
Integrated keyhole mounting tabs	Keyhole mounting tabs and flanges enable mounting to a variety of surfaces
Receptacle Color	White
AC line cord color	White
Outlets center to center measurement	38.7mm
Keyhole slot center to center measurement	Distance between keyhole tabs = 261.92mm; Distance between end tabs = 330.17
<b>CERTIFICATIONS</b>	
UL1363 (Power Tap)	UL1363 (Series Number: AGIB12015SL)
cUL / CSA (Canada)	cUL (Series Number: AGIB12015SL)
<b>WARRANTY</b>	

<b>Product Warranty Period (Worldwide)</b>	Lifetime limited warranty
--	---------------------------

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?txtModelID=2661](http://www.tripplite.com/en/products/model.cfm?txtModelID=2661).

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.