



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: PS-615-HG-OEM

### For Patient-Care Areas - Medical-Grade Power Strip with 6 Outlets and 15-ft. Cord



#### Highlights

- Versatile power distribution strip designed to be installed on any mobile cart, IV pole, etc.
- Tested to UL 1363A to supply power to plug-connected components of a movable equipment assembly that is rack-, table- or pedestal-mounted
- 6 hospital-grade receptacles and hospital-grade plug
- 15-ft. cord
- Two 15-amp resettable circuit breakers

#### Description

Tripp Lite's PS-615-HG-OEM Power Strip is designed to be installed on any mobile cart, IV pole, etc. It is designed to supply power to plug-connected components of a movable equipment assembly that is rack-, table- or pedestal-mounted. Features 6 output receptacles, 15-ft. AC power cord and two built-in resettable circuit breakers that control power to all outlets and protect against overloads. Switchless design prevents accidental shutoff. Optional-use keyhole mounting tabs and flanges.

PLUG/OUTLETS: NEMA 5-15P-HG hospital-grade plug and 6 NEMA 5-15R-HG hospital-grade receptacles

ELECTRICAL: 120V AC, 50/60Hz, 15A

FORMAT: All-metal corded multi-outlet strip

#### Applications

- Mobile carts, IV poles and other UL 1363A usages.
- Can be used in Patient Care areas, when properly mounted

#### Package Includes

- PS-615-HG-OEM
- User manual with warranty information

#### Features

- Versatile power distribution strip designed to be installed on any mobile cart, IV pole, etc.
- Meets UL 1363A
- 6 x NEMA 5-15R-HG hospital-grade output receptacles
- 15-ft. AC cord with integrated, molded NEMA 5-15P-HG hospital-grade plug
- Rugged all-metal housing withstands years of use without breakage
- 15A electrical capacity with two built-in resettable circuit breakers
- 120V, 50/60Hz
- Optional-use keyhole mounting tabs and flanges
- Switchless design prevents accidental shutoff

Specifications

|                                      |  |
|--------------------------------------|--|
| OVERVIEW                             |  |
| Model Type                           | For Patient-Care Areas   |
| OUTPUT                               |  |
| Frequency compatibility              | 50 / 60 Hz   |
| Circuit Breaker (amps)               | 15   |
| Overload protection                  | 2 x 15amp breaker (1 line, 1 neutral)                                      |
| Outlet quantity / type               | 6 NEMA 5-15R-HG  |
| Outlet orientation                   | Single row of 6  |
| INPUT                                |  |
| Nominal Input Voltage(s) Supported   | 120V AC  |
| Recommended Electrical Service       | 15A, 120V  |
| Input connection type                | NEMA 5-15P-HG  |
| Input cord length (ft.)              | 15   |
| Input cord length (m)                | 4.572  |
| Input cord gauge, type               | 14 gauge, SJT  |
| Voltage compatibility (VAC)          | 120  |
| LEDS ALARMS & SWITCHES               |  |
| Switches                             | No power switch  |
| PHYSICAL                             |  |
| Shipping weight (lbs)                | 3.55   |
| Shipping weight (kg)                 | 1.61   |
| Unit Dimensions (HWD/in)             | 13.75 x 2.5 x 1.5  |
| Unit Dimensions (HWD/cm)             | 34.93 x 6.35 x 3.81  |
| Shipping Dimensions (HWD/in)         | 15 x 6 x 3.55  |
| Shipping Dimensions (HWD/cm)         | 38.1 x 15.24 x 9.02  |
| Unit weight (lbs)                    | 2.25   |
| Unit weight (kg)                     | 1.02   |
| Material of construction             | Metal  |
| Integrated keyhole mounting tabs     | Keyhole mounting tabs and flanges enable mounting to a variety of surfaces |
| Receptacle Color                     | White  |
| AC line cord color                   | White  |
| Outlets center to center measurement | 38.7mm   |

|   |                                      |
|---|--------------------------------------|
| Keyhole slot center to center measurement | Distance between end tabs = 330.20mm |
| <b>CERTIFICATIONS</b>                     |                                      |
| Additional International Approvals        | TUV tested to UL 1363A               |
| <b>WARRANTY</b>                           |                                      |
| Product Warranty Period (Worldwide)       | Lifetime limited warranty            |

## Related Items

### Optional Products

| Related Model           | Description                | Qty. |
|-------------------------|----------------------------|------|
| <a href="#">PSCLAMP</a> | Power Strip Mounting Clamp | 1    |

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?txtModelID=3719](http://www.tripplite.com/en/products/model.cfm?txtModelID=3719).

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.