



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: RS-0615-R

1U Rackmount Power Strip with 6 Rear-Facing Outlets and 15-ft. Cord

Highlights

- 6 rear facing outlets
- 15 ft. cord
- 19" 1U rackmount
- All-metal housing



Description

Tripp Lite's RS-0615-R power strip offers 15 amp capacity AC power distribution in a versatile multi-mount cabinet. Detachable mounting flanges are configurable for rackmount, wallmount and under-counter installation. Uses only 1 rack space (1U) when installed in any 19 inch rack meeting EIA standards. Unfiltered electrical pass-through makes RS-0615-R ideal for distributing alternate waveform UPS or generator power in rack enclosures, network closets and more. Includes 6 rear-facing NEMA5-15R outlets, 15 ft AC power cord and lighted switch with latching safety cover prevents risk of accidental turn-off.

PLUG/OUTLETS: Input: NEMA 5-15P/Output: 6 Rear-facing NEMA5-15R

ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires standard NEMA 5-15R wall receptacle)

FORMAT: Supports 19 in. rackmount (uses 1 rack space/1U), wallmount, under-counter and more

Applications

- Offers multiple outlet power distribution for multiple loads in 19 inch rackmount, wallmount and under-counter applications, such as internetworking, PC systems, telecommunications, audio/video, security, sound reinforcement and more. Ideal for distribution of UPS, generator or commercially derived AC power to protected equipment.

Package Includes

- RS-0615-R Power Strip
- Warranty information
- Instruction manual

Features

- Versatile all-metal cabinet with detachable mounting flanges allows rackmount, wallmount, undercounter and other creative mounting options
- Uses one rack space (1U) in standard 19 inch rack ("zero U" mounting possible in many racks)
- Unfiltered electrical pass-through reliably distributes alternate waveform AC power from UPS or generator to supported equipment
- 6 rear facing NEMA5-15R output receptacles
- 15 foot AC cord NEMA5-15P plug connection
- Lighted power switch confirms power on/off status

- Latching switch guard prevents accidental turn off
- 15 amp electrical capacity with circuit breaker
- 120VAC, 50/60Hz electrical compatibility

Specifications

OUTPUT	
Frequency compatibility	50 / 60 Hz
Circuit Breaker (amps)	15
Outlet quantity / type	6 NEMA 5-15R
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input connection type	NEMA 5-15P
Input cord length (ft.)	15
Input cord length (m)	4.572
Voltage compatibility (VAC)	120
LEDS ALARMS & SWITCHES	
Switches	Red illuminated 2 positon switch controls power to all outlets
Locking switch cover	Transparent locking switch cover prevents accidental shutoff
PHYSICAL	
Unit Dimensions (HWD/in)	1.75 (1U) x 17.5 x 4.5
Unit Dimensions (HWD/cm)	4.445 x 44.45 x 11.4
Unit weight (lbs)	4.5
Unit weight (kg)	2.04
Material of construction	Sheet metal
Receptacle Color	Black
AC line cord color	Black
Form factors supported	1U rackmount, wall-mount and undercounter installation supported
Outlets center to center measurement	Distance between grouped outlets = 38.90mm; Distance between groups = 75.4mm; Distance between duplex outlets = 114.3mm
SPECIAL FEATURES	
TVSS grounding	Back panel nut and bolt grounding lug
CERTIFICATIONS	
NOM (Mexico)	NOM
UL1363 (Power Tap)	UL1363 (UR status)
cUL / CSA (Canada)	cUL
WARRANTY	

Product Warranty Period (Worldwide)	Lifetime limited warranty
--	---------------------------

Related Items

Optional Products

Related Model	Description	Qty.
PDUSIDEBRKT	Enables Vertical Installation of Select 1U PDUs, Power Strips and Surge Suppressors in SmartRack Configurations	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=1951.

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.