



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: RS-1215-20T

1U Rackmount Power Strip with 12 Outlets, 20A Circuit Breaker and 15-ft. Cord

Highlights

- Designed for standard 19-in. racks (1U high)
- 12 NEMA5-15/20R outlets (6 front/6 rear)
- 15-ft. cord with locking NEMA L5-20P input plug
- 20A circuit breaker



Description

Tripp Lite's RS-1215-20T Power Strip offers 20A capacity AC power distribution in a versatile multi-mount cabinet. Detachable mounting flanges are configurable for rackmount, wallmount and under-counter installation. Uses only 1 rack space (1U) when installed in any 19-in. rack meeting EIA standards. Unfiltered electrical pass-through makes RS-1215-20T ideal for distributing alternate waveform UPS or generator power in rack enclosures, network closets and more. Includes 12 NEMA5-15/20R outlets (6 front/6 rear), 15-ft. AC power cord with locking NEMA L5-20P input plug and lighted switch with cover that prevents risk of accidental turn-off.

PLUG/OUTLETS: Input: NEMA L5-20P Output: 12 x NEMA5-15/20R (6 front/6 rear)

ELECTRICAL: 120V AC, 50/60Hz, 20A (Requires NEMA 5-20R wall receptacle)

FORMAT: 19-in. rackmount (uses 1 rack space/1U), wallmount, under-counter and more

Applications

- Multiple-outlet power distribution for multiple loads in 19-in. rackmount, wallmount and under-counter applications, such as internetworking, PC systems, telecommunications, audio/video, security, sound reinforcement and more. Ideal for distribution of UPS, generator or commercially derived AC power to protected equipment.

Features

- Versatile all-metal cabinet with detachable mounting flanges allows rackmount, wallmount, undercounter and other creative mounting options
- Uses one rack space (1U) in standard 19-in. rack ("zero U" mounting possible in many racks)
- Unfiltered electrical pass-through reliably distributes alternate waveform AC power from UPS or generator to supported equipment
- 12 x NEMA5-15/20R output receptacles (6 front/6 rear)
- 15-ft. AC cord with NEMA L5-20P input plug
- Lighted power switch confirms power on/off status
- Snap-in switch guard prevents accidental turn-off
- 20A electrical capacity with circuit breaker
- 120V AC, 50/60Hz electrical compatibility

Specifications

OUTPUT	
Frequency compatibility	50 / 60 Hz
Overload protection	20A circuit breaker
Outlet quantity / type	12 NEMA 5-15/20R
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	20A 120V dedicated line
Input connection type	NEMA L5-20P
Input cord length (ft.)	15
Input cord length (m)	4.57
Voltage compatibility (VAC)	120
LEDS ALARMS & SWITCHES	
Switches	Lighted power switch
Locking switch cover	Yes
PHYSICAL	
Shipping weight (lbs)	6
Shipping weight (kg)	2.7
Unit Dimensions (HWD/in)	1.75 (1U) x 17.5 x 4.5
Unit Dimensions (HWD/cm)	4.3 x 44.4 x 11.4
Shipping Dimensions (HWD/in)	2.25 x 20.5 x 9.5
Shipping Dimensions (HWD/cm)	5.7 x 52.1 x 24.1
Unit weight (lbs)	5.4
Unit weight (kg)	2.4
Material of construction	Steel
Mounting accessories included	1U rackmount flanges
Receptacle Color	Black
AC line cord color	Black
Form factors supported	1U rackmount, wallmount
Outlets center to center measurement	Distance between Front outlets = 51.6mm; Distance between Rear outlets = 71.1mm
CERTIFICATIONS	
Approvals	UL-recognized (USA)/cUR (Canada)
WARRANTY	

Product Warranty Period (Worldwide)	Lifetime limited warranty
--	---------------------------

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=3133.

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.