



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: RS1215-HG

NOT For Patient Areas - 1U Rackmount Power Strip with 12 Hospital-Grade Outlets and 15-ft. Cord

Highlights

- Designed for standard 19-inch racks (1U high)
- 12 hospital-grade outlets (6 front / 6 rear)
- 15-ft. cord with hospital-grade plug
- 15A resettable circuit breaker
- Illuminated On/Off switch with locking safety cover



Description

Tripp Lite's RS-1215-HG all-metal Power Strip offers 15A capacity AC power distribution in a versatile multi-mount cabinet. Detachable mounting flanges are configurable for rackmount, wallmount and under-counter installation. Uses only 1 rack space (1U) when installed in any 19-in. rack meeting EIA standards. Unfiltered electrical pass-through makes the RS-1215-HG ideal for distributing alternate waveform UPS or generator power in rack enclosures, network closets and more. Features Hospital Grade plug and outlets. Includes 12 outlets (6 front/6 rear), 15-ft. AC power cord and lighted switch with cover to prevent accidental turn-off.

PLUG/OUTLETS: NEMA 5-15P-HG hospital-grade plug and 12 NEMA 5-15R-HG hospital-grade outlets (6 front/6 rear)

ELECTRICAL: 120V AC, 50/60Hz, 15A

FORMAT: 19-in. rackmount (1U)

Applications

- AC power distribution with hospital-grade receptacles and plug where durability and reliability are required. Not for use where NEC requires hospital-grade receptacles.

Package Includes

- RS-1215-HG Rackmount Power Strip
- Instruction manual with warranty information

Features

- Versatile all-metal cabinet with detachable mounting flanges allows rackmount, wallmount, undercounter and other creative mounting options
- Unfiltered electrical pass-through reliably distributes alternate waveform AC power from UPS or generator to supported equipment
- Uses one rack space (1U) in standard 19-in. rack ("zero U" mounting possible in many racks)
- 12 x NEMA 5-15R-HG hospital-grade output receptacles (6 front/6 rear), each pair with green-dot hospital-grade designation
- 15-ft. 14-gauge AC cord with high-impact resistant NEMA 5-15P-HG hospital-grade plug
- Lighted power switch (with safety cover) confirms power on/off status
- Snap-in switch guard prevents accidental turn-off
- 15A electrical capacity with resettable circuit breaker

- 120V AC, 50/60Hz electrical compatibility

Specifications

OVERVIEW	
Model Type	NOT For Patient Areas
OUTPUT	
Frequency compatibility	50 / 60 Hz
Circuit Breaker (amps)	15
Outlet quantity / type	12 NEMA 5-15R-HG
Outlet orientation	6 front / 6 rear
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input connection type	NEMA 5-15P-HG
Input cord length (ft.)	15
Input cord length (m)	4.572
Voltage compatibility (VAC)	120
LEDS ALARMS & SWITCHES	
Switches	Red illuminated 2 positon switch controls power to all outlets
Locking switch cover	Transparent locking switch cover prevents accidental shutoff
PHYSICAL	
Unit Dimensions (HWD/in)	1.75 x 17.3 x 4
Unit Dimensions (HWD/cm)	4.4 x 43.9 x 10.2
Unit weight (lbs)	4.6
Unit weight (kg)	2.09
Material of construction	Sheet metal
Receptacle Color	White
AC line cord color	Black
Form factors supported	1U rackmount, wallmount and undercounter installation supported
Outlets center to center measurement	Distance between Front outlets = 83.35mm; Distance between Rear outlets = 165.1mm
SPECIAL FEATURES	
TVSS grounding	Back panel nut and bolt grounding lug
CERTIFICATIONS	
UL1363 (Power Tap)	UL1363 (UR status) (Series Number: AGIP120V6IPRM)
cUL / CSA (Canada)	cUL (Series Number: AGIP120V6IPRM)
WARRANTY	

Product Warranty Period (Worldwide)	Lifetime limited warranty
--	---------------------------

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=204.

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.