



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: SUPER7COAX

7-outlet, 7-ft cord, 2160 joule, Coaxial protection, Protect It! Surge Suppressor



Highlights

- 7 outlets/7 ft. cord
- 2160 joule rating
- 2.2 GHz gold coaxial surge protection
- \$75,000 [Ultimate Lifetime Insurance](#) (USA, Puerto Rico & Canada only)

Description

The SUPER7COAX surge suppressor from Tripp Lite has 7 outlets and a 7-ft. cord with a space-saving right-angle plug. The unit has 2160 joules of surge energy absorption to handle the strongest surges. Built-in 2.2 GHz gold coax jacks prevent surges from damaging your cable/satellite equipment. Diagnostic LEDs alert the user to potential power problems. \$75,000 [Ultimate Lifetime Insurance](#) (USA and Canada Only).

Applications

- Audio/visual devices, cable television connections, home theater systems, personal computers, CAD/CAM/CAE workstations, network nodes, file servers, point-of-sale terminals, and more.

Package Includes

- Super7Coax Surge Suppressor
- 6-ft gold coax cable
- Warranty information with instruction manual

Features

- 7 outlets
- 7-ft. cord with space-saving right-angle plug
- Surge suppression rating: 2160 joules
- 1 set of 2.2 GHz gold coaxial jacks
- EMI/RFI noise filtering
- Can accommodate up to 3 transformers without blocking remaining outlets
- \$75,000 [Ultimate Lifetime Insurance](#) (USA and Canada Only) covers connected equipment
- Diagnostic LEDs indicate protection present & ground present
- Keyhole supports for wall mounting

Specifications

OVERVIEW	
Intended Application	Home/Office, Audio/Video
OUTPUT	
Frequency compatibility	50 / 60 Hz

Output watts	1800
Circuit Breaker (amps)	15
Outlet quantity / type	7 NEMA 5-15R
Transformer accommodation	Supports 3 large transformer plug accessories without covering remaining outlets, accepts up to 5 transformers total
Outlet orientation	Single row of 5, plus 2 side mounted outlets
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input connection type	NEMA 5-15P
Input plug features	Space-saving right angle input plug
Input cord length (ft.)	7
Input cord length (m)	2.13
Input cord gauge, type	14 gauge, SJT
Voltage compatibility (VAC)	120
Maximum Surge Amps	144000
LEDS ALARMS & SWITCHES	
Switches	Two position on/off power switch
Diagnostic LEDs	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
SURGE / NOISE SUPPRESSION	
AC suppression joule rating	2160
AC suppression response time	< 1 ns
Protection modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping voltage (RMS)	150
UL1449 let through rating	330V L-G; 400V L-N; 400V N-G
EMI / RFI filtering	Up to 20 dB
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	Yes
Cable (Coax) Protection Details	1 line
Network (Ethernet) Protection	No
PHYSICAL	
Shipping weight (lbs)	1.56
Shipping weight (kg)	0.71
Unit Dimensions (HWD/in)	1.54 x 2.72 x 10.3

Unit Dimensions (HWD/cm)	3.91 x 6.91 x 26.16
Shipping Dimensions (HWD/in)	12.40 x 5.90 x 1.77
Shipping Dimensions (HWD/cm)	31.50 x 14.99 x 4.50
Unit weight (lbs)	1.39
Unit weight (kg)	0.63
Material of construction	Plastic
Integrated keyhole mounting tabs	Keyhole mounting tabs enable wall mounting
Housing Color	Light Gray
Receptacle Color	Light gray
AC line cord color	Light Gray
Style	Strip
Outlets center to center measurement	Between Standard Outlets = 29mm; Between Transformer Outlets = 48mm
Keyhole slot center to center measurement	Distance Between Slots = 78mm; Distance Between Slot Height = 24mm
SPECIAL FEATURES	
Right-Angle Plug	Yes
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL1449 3RD EDITION
UL1363 (Power Tap)	UL1363
UL497A (Communications)	UL497A
FCC Part 68 (Communications)	FCC Part 68
cUL / CSA (Canada)	cUL
Industry Canada (Communications)	Industry Canada
Approvals	Exceeds IEEE 587 category A&B specifications
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$75,000 Ultimate Lifetime Insurance

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=129.

improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.