



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: SWIVEL6

### 6 rotatable outlets, direct plug-in, 1500 joule - Protect It! Surge Suppressor



#### Highlights

- 6 rotatable outlets
- Direct plug-in design
- 1500 joule rating
- Diagnostic LEDs
- \$20,000 [Ultimate Lifetime Insurance](#) (USA, Puerto Rico & Canada only)

#### Description

The SWIVEL6 offers reliable surge and line noise protection. Premium features include a compact, direct plug-in design for easy portability, six rotatable outlets for easier plug connection and removal and 1500 joules of surge absorption protection. Diagnostic LEDs alert you to potential wiring or protection faults before connected equipment is damaged. \$20,000 [Ultimate Lifetime Insurance](#) (USA, Puerto Rico and Canada only).

#### Applications

- Ideal for any desktop, network or home computing application requiring AC protection.

#### Package Includes

- SWIVEL6 Surge Suppressor
- Instruction manual with warranty information

#### Features

- 6 rotatable outlets allow for easier plug connection and removal
- 1500 joules surge suppression rating with EMI/RFI line noise filtering help components perform at their peak (sharper, crisper video; deeper, fuller audio and longer component life spans)
- 2 diagnostic LEDs alert user to protection and grounding status
- High-impact plastic housing (black) stands up to the most demanding environments
- Direct plug-in design converts two outlets into six by plugging into any wall outlet
- \$20,000 [Ultimate Lifetime Insurance](#) (USA and Canada Only)

#### Specifications

OVERVIEW	
Intended Application	Home/Office
OUTPUT	
Frequency compatibility	60 Hz
Circuit Breaker (amps)	15

Outlet quantity / type	6 NEMA 5-15R
Outlet orientation	Rotatable
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input connection type	NEMA 5-15P
Input cord length details	Direct plug-in
Voltage compatibility (VAC)	120
Maximum Surge Amps	60000
<b>LEDS ALARMS &amp; SWITCHES</b>	
Diagnostic LEDs	Built-in LEDs confirm suppressor "protected" (green) and "grounded" (red) status
<b>SURGE / NOISE SUPPRESSION</b>	
AC suppression joule rating	1500
AC suppression response time	< 1 ns
Protection modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping voltage (RMS)	330
UL1449 let through rating	400, 500, 500
EMI / RFI filtering	Up to 20 dB
<b>DATALINE SURGE SUPPRESSION</b>	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
<b>PHYSICAL</b>	
Shipping weight (lbs)	1.0
Shipping weight (kg)	0.45
Unit Dimensions (HWD/in)	6.25 x 4 x 2.25
Unit Dimensions (HWD/cm)	15.88 x 10.16 x 5.72
Shipping Dimensions (HWD/in)	8.6 x 5.8 x 2.38
Shipping Dimensions (HWD/cm)	21.84 x 14.73 x 6.05
Unit weight (lbs)	0.6
Unit weight (kg)	0.27
Material of construction	Plastic
Housing Color	Black

<b>Receptacle Color</b>	Black
<b>Style</b>	Direct Plug-in
<b>Outlets center to center measurement</b>	29mm
<b>CERTIFICATIONS</b>	
<b>UL1449 3rd Edition (AC Suppression)</b>	UL1449 3RD EDITION
<b>cUL / CSA (Canada)</b>	cUL
<b>Approvals</b>	RoHS
<b>WARRANTY</b>	
<b>Product Warranty Period (Worldwide)</b>	Lifetime limited warranty
<b>Connected Equipment Insurance (U.S., Canada &amp; Puerto Rico)</b>	\$20,000 <a href="#">Ultimate Lifetime Insurance</a>

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?txtModelID=3617](http://www.tripplite.com/en/products/model.cfm?txtModelID=3617).

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.