



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: TLM609GF

### Power It! Safety Power Strip with 6 Outlets and 9-ft. Cord with GFCI Plug



#### Highlights

- 6 outlets (including transformer outlets and 4 safety covers)
- 9 ft. cord with GFCI plug
- Cord wrap with hang holes
- Rugged metal case

#### Description

This Tripp Lite power strip is designed to safely distribute power to connected equipment in harsh environments. It provides a convenient source for multiple outlets wherever they're needed. 6 outlets distribute AC power to a wide range of power tools, drill presses, air compressors, power sanders and more. Convenient transformer outlets accommodate multiple transformers without blocking other outlets. A 9 ft. grounded cord with integrated cord clip reaches distant outlets. A GFCI plug protects users from electrical shock in wet or humid environments. A lighted on/off switch provides power control over connected equipment. 4 safety covers shield unused outlets from debris and accidental contact. A rugged metal case stands up to the harshest environments. Built-in cord wrap with hang holes provides convenient cord management. Integrated keyhole slots on bottom panel provide convenient wall/desk mounting. Its bright yellow color alerts you and others that power cords and tools are in use.

#### Applications

- Industrial
- Automotive
- Factory
- Hardware

#### Package Includes

- TLM609GF Safety Power Strip
- 4 safety covers
- Owner's manual

#### Features

- 6 outlets distribute AC power to a wide range of band saws, drill presses, air compressors, power sanders and more.
- Convenient transformer outlets accommodate multiple transformers without blocking other outlets.
- A 9 ft. grounded cord with integrated cord clip reaches distant outlets.
- A GFCI plug protects users from electrical shock in wet or humid environments.
- A lighted on/off switch with integrated 15 amp circuit breaker provides power control and overload protection over connected equipment.
- 4 safety covers shield unused outlets from debris and accidental contact.
- A rugged metal case stands up to the harshest environments.
- Built-in cord wrap with hang holes provides convenient cord management.
- Integrated keyhole slots on bottom panel provide convenient wall/desk mounting.

- Its bright yellow color alerts you and others that power cords and tools are in use.
  - OSHA color guidelines, outlined in Document 1910.145, alert users to hazardous situations, which may cause minor or moderate injury.
- This Tripp Lite product complies with those guidelines.

## Specifications

OUTPUT	
Frequency compatibility	60 Hz
Circuit Breaker (amps)	15
Overload protection	GFCI plug
Outlet quantity / type	6 NEMA 5-15R
Transformer accommodation	Yes (2)
Outlet safety covers	Yes (4)
Outlet orientation	Single row
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V, 15A
Input connection type	GFCI 5-15P
Input plug features	Integrated cord clip plus GFCI breaker
Input cord length (ft.)	9
Input cord length (m)	2.74
Input cord gauge, type	14 gauge, SJT
Voltage compatibility (VAC)	120
LEDS ALARMS & SWITCHES	
Switches	Combination AC circuit breaker and 2 position red illuminated on/off power switch
PHYSICAL	
Shipping weight (lbs)	3.33
Shipping weight (kg)	1.51
Unit Dimensions (HWD/in)	15.97 x 3.07 x 1.61
Unit Dimensions (HWD/cm)	40.56 x 7.80 x 4.09
Shipping Dimensions (HWD/in)	16.17 x 7.10 x 2.7
Shipping Dimensions (HWD/cm)	41.07 x 18.03 x 6.86
Unit weight (lbs)	3.24
Unit weight (kg)	1.47
Material of construction	All-metal

<b>Integrated keyhole mounting tabs</b>	Yes
<b>Receptacle Color</b>	black
<b>AC line cord color</b>	yellow
<b>Outlets center to center measurement</b>	Distance between standard outlets = 30.40mm; Distance between standard outlets and transformer outlets = 45mm
<b>Keyhole slot center to center measurement</b>	209.55mm
<b>CERTIFICATIONS</b>	
<b>Approvals</b>	cULus, RoHS
<b>WARRANTY</b>	
<b>Product Warranty Period (Worldwide)</b>	Lifetime limited warranty

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?txtModelID=3675](http://www.tripplite.com/en/products/model.cfm?txtModelID=3675).

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.