

Model #: TLP1008TEL

10 outlet, 8ft cord, 2395 joules, Tel/modem protection - Protect It! Surge Suppressor



Highlights

- 10 outlets / 8-ft. cord
- 2395 joule rating
- 1 in/2 out tel/modem surge protection
- 4 transformer spaces
- \$150,000 Ultimate Lifetime Insurance (USA & Canada only)

Description

Tripp Lite's TLP1008TEL offers economical AC surge suppression for protection of workstations, PCs, telecom systems, home electronics and other sensitive equipment. The TLP1008TEL features 10 outlets, an 8-ft. cord with a space-saving right-angle plug, and diagnostic LEDs to warn of suppressor damage. The unit has a surge suppression rating of 2395 joules to shield equipment from line noise and the strongest surges. Built-in RJ11 jacks prevent surges from damaging your modem/fax/phone equipment. \$150,000 Ultimate Lifetime Insurance (USA & Canada only)

PLUG/OUTLETS: Input: NEMA5-15P/Output: 10 NEMA5-15R/8-ft. AC line cord

ELECTRICAL: 120V AC, 50/60Hz, 15A (requires NEMA5-15R wall receptacle)

FORMAT: Corded multi-outlet strip with 5 transformer-spaced outlet

SUPPRESSION: AC: 150V RMS Clamping/2395 joules/400V UL1449 3rd Edition

Applications

• Ideal for home computers, TV/VCR/DVD players, stereos and other important electrical equipment

Package Includes

- TLP1008TEL surge suppressor
- 6-ft. RJ11 telephone cord
- Instruction manual with warranty information

Features

- 10 outlets with integrated child safety covers
- 8-ft. cord with space-saving right-angle plug
- Built-in RJ11 jacks prevent surges from damaging your modem/fax equipment built-in splitter protects two devices sharing a single line; 6-ft. telephone cord included
- Surge suppression rating: 2395 joules
- EMI/RFI noise filtering
- 15 amp resettable circuit breaker
- Diagnostic LEDs confirm suppressor "protection present" (green) and "grounded" (red) status

- Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
- Can accommodate up to 4 transformers without blocking remaining outlets
- \$150,000 Ultimate Lifetime Insurance (USA and Canada Only) covers connected equipment
- Keyhole supports for wall mounting
- Failsafe shutdown mode
- Lighted power switch

Specifications

OVERVIEW		
Intended Application	Home/Office	
OUTPUT		
Frequency compatibility	50 / 60 Hz	
Output watts	1800W	
Circuit Breaker (amps)	15A	
Overload protection	15A resettable circuit breaker	
Outlet quantity / type	10 NEMA 5-15R	
Transformer accommodation	Supports 4 large transformer plug accessories without covering remaining outlets, accepts up to 8 transformers total	
Outlet safety covers	Includes built-in sliding outlet safety covers	
Outlet orientation	Two rows of outlets, including 4 widely spaced for transformers	
INPUT		
Nominal Input Voltage(s) Supported	120V AC	
Recommended Electrical Service	120V (110-125V)	
Input connection type	NEMA 5-15P	
Input plug features	Space-saving right angle input plug	
Input cord length (ft.)	8	
Input cord length (m)	2.4	
Input cord gauge, type	14 gauge, SJT	
Voltage compatibility (VAC)	120	
Maximum Surge Amps	120000	
LEDS ALARMS & SWITCHES		
Switches	Combination AC circuit breaker and two-position on/off power switch	
Diagnostic LEDs	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status	
SURGE / NOISE SUPPRESSION	SURGE / NOISE SUPPRESSION	
AC suppression joule rating	2395	
AC suppression response time	< 1 ns	
Protection modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression	

Clamping voltage (RMS)	150V	
UL1449 let through rating	400V - UL Verified	
EMI / RFI filtering	Up to 40dB	
DATALINE SURGE SUPPRESSION		
Telephone/DSL Protection	Yes	
Telephone/DSL Protection Details	1 line	
Cable (Coax) Protection	No	
Network (Ethernet) Protection	No	
PHYSICAL		
Unit Dimensions (HWD/in)	12 x 5.25 x 2	
Unit Dimensions (HWD/cm)	30.48 x 13.33 x 5.08	
Shipping Dimensions (HWD/in)	14 x 7.75 x 2.25	
Shipping Dimensions (HWD/cm)	35.56 x 19.69 x 5.72	
Unit weight (Ibs)	2	
Unit weight (kg)	0.91	
Material of construction	Plastic	
Integrated keyhole mounting tabs	Keyhole mounting tabs enable wall mounting	
Housing Color	Black	
Receptacle Color	Black	
AC line cord color	Black	
Style	Strip	
Outlets center to center measurement	Between Standard Outlets = 28.4mm; Between Standard and Transformer Outlets = 56.8mm	
Keyhole slot center to center measurement	108mm	
SPECIAL FEATURES		
Right-Angle Plug	Yes	
CERTIFICATIONS		
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition	
UL1363 (Power Tap)	UL1363	
UL497A (Communications)	UL497A	
FCC Part 68 (Communications)	FCC Part 68	
cUL / CSA (Canada)	cUL	

Industry Canada (Communications)	Industry Canada	
Approvals	Exceeds IEEE 587 category A&B specifications	
WARRANTY		
Product Warranty Period (Worldwide)	Lifetime limited warranty	
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$150,000 Ultimate Lifetime Insurance	

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModeIID=2634.

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.