



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: TLP1208TEL

### 12 outlet, 8-ft cord, 2160 joules, Tel/Modem Protection - Protect It! Surge Suppressor



#### Highlights

- 12 outlets / 8-ft. cord
- 2160 joule rating
- 1in/2 out tel/modem surge protection
- 4 transformer spaces
- \$150,000 Ultimate Lifetime Insurance (USA & Canada only)

#### Description

Tripp Lite's TLP1208TEL offers economical AC surge suppression for protection of workstations, PCs, telecom systems, home electronics and other sensitive equipment. The TLP1208TEL features 12 outlets, an 8-ft. cord with a space-saving right-angle plug, and diagnostic LEDs to warn of suppressor damage. The unit has a surge suppression rating of 2160 joules to shield equipment from line noise and the strongest surges. Built-in RJ11 jacks prevent surges from damaging your modem/fax/phone equipment. \$150,000 Ultimate Lifetime Insurance (USA & Canada only)

PLUG/OUTLETS: Input: NEMA5-15P/Output: 12 NEMA5-15R/8-ft. AC line cord

ELECTRICAL: 120V AC, 50/60Hz, 15A (requires NEMA5-15R wall receptacle)

FORMAT: Corded multi-outlet strip with 4 transformer-spaced outlet

SUPPRESSION: AC: 150V RMS Clamping/2160 joules/330V L-G, 400V L-N, 400V N-G UL1449 3rd Edition

#### Applications

- Ideal for home computers, TV/VCR/DVD players, stereos and other important electrical equipment

#### Package Includes

- TLP1208TEL surge suppressor
- 6-ft. RJ11 telephone cord
- Instruction manual with warranty information

#### Features

- 12 outlets with integrated child safety covers
- 8-ft cord with space-saving right-angle plug
- Built-in RJ11 jacks prevent surges from damaging your modem/fax equipment; 6-ft telephone cord included
- Surge suppression rating: 2160 joules
- EMI/RFI noise filtering
- 15 amp resettable circuit breaker
- Diagnostic LEDs confirm suppressor "protection present" (green) and "grounded" (red) status

- Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
- Can accomodate up to 4 transformers without blocking remaining outlets
- Keyhole supports for wall mounting
- \$150,000 Ultimate Lifetime Insurance (USA and Canada Only) covers connected equipment

## Specifications

OVERVIEW	
Intended Application	Home/Office
OUTPUT	
Output Volt Amp Capacity (VA)	15
Output Watt Capacity (watts)	1875
Frequency compatibility	50 / 60 Hz
Overload protection	15A resettable circuit breaker
Outlet quantity / type	12 NEMA 5-15R
Transformer accommodation	Supports 4 large transformer plug accessories without covering remaining outlets, accepts up to 8 transformers total
Outlet orientation	Two rows of outlets, including 4 widely spaced for transformers
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input connection type	NEMA 5-15P
Input plug features	Space-saving right angle input plug
Input cord length (ft.)	8
Input cord length (m)	2.4
Input cord gauge, type	14 gauge, SJT
Voltage compatibility (VAC)	120
Maximum Surge Amps	144000
LEDS ALARMS & SWITCHES	
Switches	Two-position on/off power switch
Diagnostic LEDs	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
SURGE / NOISE SUPPRESSION	
AC suppression joule rating	2160
AC suppression response time	< 1 ns
Protection modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping voltage (RMS)	150
UL1449 let through rating	330V L-G, 400V L-N, 400V N-G

EMI / RFI filtering	Up to 40dB
<b>DATALINE SURGE SUPPRESSION</b>	
Telephone/DSL Protection	Yes
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
<b>PHYSICAL</b>	
Shipping weight (lbs)	2.27
Shipping weight (kg)	1.03
Unit Dimensions (HWD/in)	1.54 x 2.72 x 10.30
Unit Dimensions (HWD/cm)	3.91 x 6.91 x 26.16
Shipping Dimensions (HWD/in)	2.05 x 8.66 x 13.39
Shipping Dimensions (HWD/cm)	5.21 x 22.00 x 34.01
Unit weight (lbs)	2.09
Unit weight (kg)	0.95
Material of construction	Plastic
Integrated keyhole mounting tabs	Keyhole mounting tabs enable wall mounting
Housing Color	Silver
Receptacle Color	Black
AC line cord color	Black
Style	Strip
Outlets center to center measurement	Distance between standard outlets = 25.4mm; Distance between transformer outlets = 57mm
Keyhole slot center to center measurement	Distance between horizontal tabs = 152mm; Distance between vertical tabs = 73.5mm
<b>SPECIAL FEATURES</b>	
Right-Angle Plug	Yes
<b>CERTIFICATIONS</b>	
UL1449 3rd Edition (AC Suppression)	UL1449 3RD EDITION
UL1363 (Power Tap)	UL1363
UL497A (Communications)	UL497A
FCC Part 68 (Communications)	FCC Part 68
cUL / CSA (Canada)	cUL
Industry Canada (Communications)	Industry Canada

<b>Approvals</b>	Exceeds IEEE 587 category A&B specifications
<b>WARRANTY</b>	
<b>Product Warranty Period (Worldwide)</b>	Lifetime limited warranty
<b>Connected Equipment Insurance (U.S., Canada &amp; Puerto Rico)</b>	\$150,000 <a href="#">Ultimate Lifetime Insurance</a>

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?txtModelID=4463](http://www.tripplite.com/en/products/model.cfm?txtModelID=4463).

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.