



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: TLP404

4 outlets, 4-ft cord, 390 joules Protect It! Surge Suppressor



Highlights

- 4 outlets / 4-ft. cord
- 390 joule rating
- \$1000 [Ultimate Lifetime Insurance](#) (USA, Puerto Rico & Canada only)

Description

Tripp Lite's TLP404 offers economical AC surge suppression for protection of workstations, desktop PCs, telecom systems and other sensitive electronics. Built-in AC surge suppression shields connected equipment from damage and performance problems due to transient surges. TLP404 offers 4 total outlets, 4 foot cord and diagnostic LED to warn of suppressor damage. AC suppression rated at 390 joules shields equipment from surges and line noise. Attractive white suppressor housing with keyhole mounting tabs and 1 designated transformer plug outlet offers convenient protection of desktop computer equipment and accessories. \$1,000 [Ultimate Lifetime Insurance](#) (USA & Canada Only).

PLUG/OUTLETS: Input: NEMA5-15P/Output: 4 NEMA5-15R/4-ft. AC line cord

ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires NEMA5-15R wall receptacle)

FORMAT: Corded multi-outlet strip with 1 transformer spaced outlet

SUPPRESSION: AC: 150V RMS Clamping/390 joules/500V UL1449 3rd Edition

Applications

- Ideal for any desktop, network or home computing application requiring AC line protection

Package Includes

- TLP404 surge suppressor
- Instruction manual with warranty information

Features

- 4 outlets
- 4-ft. cord
- Surge suppression rating: 390 joules
- EMI/RFI noise filtering
- 15 amp resettable circuit breaker
- Diagnostic LED confirms surge protection status
- Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
- Can accommodate 1 large transformer plug without covering remaining outlets, 2 total transformers

- Keyhole supports for wall mounting
- Lighted power switch
- \$1,000 [Ultimate Lifetime Insurance](#) (USA and Canada Only)

Specifications

| OVERVIEW | |
|------------------------------------|--|
| Intended Application | Home/Office |
| OUTPUT | |
| Frequency compatibility | 50 / 60 Hz |
| Output watts | 1800 |
| Circuit Breaker (amps) | 15 |
| Overload protection | 15A resettable combo switch / circuit breaker |
| Outlet quantity / type | 4 NEMA 5-15R |
| Transformer accommodation | Supports 1 large transformer plug accessory without covering remaining outlets, accepts up to 2 transformers total |
| Outlet orientation | Single row of 4 outlets |
| INPUT | |
| Nominal Input Voltage(s) Supported | 120V AC |
| Recommended Electrical Service | 120V (110-125V) |
| Input connection type | NEMA 5-15P |
| Input cord length (ft.) | 4 |
| Input cord length (m) | 1.2 |
| Input cord gauge, type | 14 gauge, SJT |
| Voltage compatibility (VAC) | 120 |
| Maximum Surge Amps | 22500 |
| LEDS ALARMS & SWITCHES | |
| Switches | Combination AC circuit breaker and 2 position on/off power switch |
| Diagnostic LEDs | Built-in LED confirms suppressor "protection present" (green) status |
| SURGE / NOISE SUPPRESSION | |
| AC suppression joule rating | 390 |
| AC suppression response time | < 1 ns |
| Protection modes | Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression |
| Clamping voltage (RMS) | 150V |
| UL1449 let through rating | 500V - UL Verified |
| DATALINE SURGE SUPPRESSION | |
| Telephone/DSL Protection | No |

| | |
|--|--|
| Cable (Coax) Protection | No |
| Network (Ethernet) Protection | No |
| PHYSICAL | |
| Shipping weight (lbs) | 1 |
| Shipping weight (kg) | .45 |
| Unit Dimensions (HWD/in) | 8.25 x 2 x 1.5 |
| Unit Dimensions (HWD/cm) | 21 x 5.08 x 3.81 |
| Shipping Dimensions (HWD/in) | 10 x 3.50 x 1.25 |
| Shipping Dimensions (HWD/cm) | 25.4 x 8.9 x 3.175 |
| Unit weight (lbs) | 1 |
| Unit weight (kg) | .45 |
| Material of construction | Plastic |
| Integrated keyhole mounting tabs | Keyhole mounting tabs enable wall mounting |
| Housing Color | Light Gray |
| Receptacle Color | Light Gray |
| AC line cord color | Light Gray |
| Style | Strip |
| Outlets center to center measurement | 28.6mm |
| Keyhole slot center to center measurement | Distance between slots = 57.5mm; Distance between slot height = 26mm |
| CERTIFICATIONS | |
| UL1449 3rd Edition (AC Suppression) | UL1449 3rd Edition |
| UL1363 (Power Tap) | UL1363 |
| cUL / CSA (Canada) | cUL |
| Approvals | Exceeds IEEE 587 category A&B specifications |
| WARRANTY | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |
| Connected Equipment Insurance (U.S., Canada & Puerto Rico) | \$1,000 Ultimate Lifetime Insurance |

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=2631.

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.