



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: TLP4BK

4 outlet, Direct plug-in, 670 joule - Protect It! Surge Suppressor



Highlights

- 4 side-mounted outlets (including 2 transformer-friendly outlets)
- Direct plug-in design
- 670 joule rating
- Diagnostic LEDs
- \$10,000 [Ultimate Lifetime Insurance](#) (USA & Canada only)

Description

The TLP4BK Surge Suppressor from Tripp Lite has 4 side-mounted outlets (including 2 transformer-friendly outlets), a convenient direct plug-in design and diagnostic LEDs. The unit has a surge suppression rating of 670 joules to handle the strongest surges. \$10,000 [Ultimate Lifetime Insurance](#) (USA & Canada Only).

Applications

- Computers, printers/peripherals, home electronics (stereos, TV, DVD player, etc.), satellite systems, appliances, power tools, lighting and more

Package Includes

- TLP4BK Surge Suppressor
- Instruction manual with warranty information

Features

- 4 side-mounted outlets allows easier plug connection and removal (including 2 transformer-friendly outlets)
- Direct plug-in design converts two outlets into four by plugging in to any wall outlet
- Surge suppression rating: 670 joules
- EMI/RFI noise filtering
- Diagnostic LEDs indicate protection present & ground present
- \$10,000 Ultimate Lifetime Insurance (USA and Canada Only) covers connected equipment

Specifications

OVERVIEW	
Intended Application	Home/Office
OUTPUT	
Frequency compatibility	50 / 60 Hz
Circuit Breaker (amps)	15

Outlet quantity / type	4 NEMA 5-15R
Transformer accommodation	Accommodates 2 transformers
Outlet orientation	Side-mounted
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input connection type	NEMA 5-15P
Input cord length details	Direct plug-in
Voltage compatibility (VAC)	120
LEDS ALARMS & SWITCHES	
Diagnostic LEDs	Built-in LEDs confirm suppressor "protection" (green) and "grounded" (red) status
SURGE / NOISE SUPPRESSION	
AC suppression joule rating	670
AC suppression response time	< 1 ns
Protection modes	Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
Clamping voltage (RMS)	330
UL1449 let through rating	500V
EMI / RFI filtering	Up to 20 dB
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Shipping weight (lbs)	0.38
Shipping weight (kg)	0.17
Unit Dimensions (HWD/in)	3.26 x 5.80 x 1.86
Unit Dimensions (HWD/cm)	8.28 x 14.73 x 4.72
Shipping Dimensions (HWD/in)	9.44 x 5.75 x 2.15
Shipping Dimensions (HWD/cm)	23.98 x 14.61 x 5.46
Unit weight (lbs)	0.36
Unit weight (kg)	0.16
Material of construction	Plastic
Housing Color	Black
Receptacle Color	Black

Style	Direct Plug-in
Outlets center to center measurement	Distance between transformer outlets = 56mm; Distance between standard outlets = 28mm
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL1449 with fail safe circuit
FCC Part 68 (Communications)	Yes
cUL / CSA (Canada)	cUL
Approvals	RoHS
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$10,000 Ultimate Lifetime Insurance

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=3611.

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.