



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: TLP707TEL

7 outlet, 7-ft cord, 1080 joules, tel/modem protection - Protect It! Surge Suppressor



Highlights

- 7 outlets / 7-ft. cord
- 1080 joule rating
- 1 in/1 out tel/modem surge protection
- \$50,000 [Ultimate Lifetime Insurance](#) (USA, Puerto Rico & Canada only)

Description

Tripp Lite's TLP707TEL surge suppressor offers complete AC and phone line surge suppression for comprehensive protection of workstations, desktop PCs, telecom systems and other sensitive electronics. Heavy grade AC surge suppression shields connected equipment from damage and performance problems due to transient surges. Set of RJ11 telephone line suppression jacks protect dialup and DSL modem lines, fax machines, cordless phones and more. TLP707TEL offers 7 total outlets, 7 foot cord with space-saving angled plug, automatic cord management and diagnostic LEDs to warn of wiring problems and suppressor damage. Heavy grade AC suppression rated at 1080 joules shields equipment from surges and line noise. Attractive metallic silver housing with 3 designated transformer plug outlets offers convenient protection of desktop computer equipment and accessories. \$50,000 [Ultimate Lifetime Insurance](#) (USA and Canada Only).

PLUG/OUTLETS: Input: NEMA5-15P/Output: 7 NEMA5-15R/7-ft. AC line cord

ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires NEMA5-15R wall receptacle)

FORMAT: Unique on-end suppressor format supports the connection of up to 3 large transformer plugs on one side and 4 additional straight input plugs on the other

SUPPRESSION: AC: 150V RMS Clamping/1080 joules/400V UL1449 3rd Edition

Applications

- Ideal for home computers, TV/VCR/DVD players, stereos and lamps

Package Includes

- TLP707TEL surge suppressor
- 6-ft. RJ11 cable
- Instruction manual and warranty information

Specifications

OVERVIEW	
Intended Application	Home/Office
OUTPUT	

Frequency compatibility	50 / 60 Hz
Output watts	1800
Circuit Breaker (amps)	15
Overload protection	15A resettable combo switch / circuit breaker
Outlet quantity / type	7 NEMA 5-15R
Transformer accommodation	Supports 3 large transformer plug accessories without covering remaining outlets, accepts up to 6 transformers total
Outlet safety covers	Includes built-in sliding outlet safety covers
Outlet orientation	Two rows of outlets, 3 widely spaced on one side for transformers, 4 closely spaced outlets on the other
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input connection type	NEMA 5-15P
Input plug features	Space-saving right angle input plug
Input cord length (ft.)	7
Input cord length (m)	2.13
Input cord gauge, type	14 gauge, SJT
Voltage compatibility (VAC)	120
Maximum Surge Amps	72000
LEDS ALARMS & SWITCHES	
Switches	Combination AC circuit breaker and 2 position on/off power switch
Diagnostic LEDs	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
SURGE / NOISE SUPPRESSION	
AC suppression joule rating	1080
AC suppression response time	< 1 ns
Protection modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping voltage (RMS)	150
UL1449 let through rating	400V
EMI / RFI filtering	Up to 20dB
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	No
Network (Ethernet) Protection	No

PHYSICAL	
Shipping weight (lbs)	1.41
Shipping weight (kg)	0.64
Unit Dimensions (HWD/in)	1.97 x 1.61 x 10.91
Unit Dimensions (HWD/cm)	5.00 x 4.09 x 27.71
Shipping Dimensions (HWD/in)	12.40 x 4.92 x 2.25
Shipping Dimensions (HWD/cm)	31.50 x 12.50 x 5.72
Unit weight (lbs)	1.25
Unit weight (kg)	0.57
Material of construction	Plastic
Housing Color	Metallic Silver
Receptacle Color	Gray
AC line cord color	Black
Style	Strip
Form factors supported	Supports floor / desktop placement
Outlets center to center measurement	Transformer Side Spacing = 61.8mm; Standard Outlet Side Spacing = 25.4mm
SPECIAL FEATURES	
Appearance	Unique on-end suppressor format supports the connection of up to 3 large transformer plugs on one side and 4 additional straight input plugs on the other.
Right-Angle Plug	Yes
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL1449 3RD EDITION
UL1363 (Power Tap)	UL1363
UL497A (Communications)	UL497A
FCC Part 68 (Communications)	FCC Part 68
cUL / CSA (Canada)	cUL
Industry Canada (Communications)	Industry Canada
Approvals	Exceeds IEEE 587 category A&B specifications
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$50,000 Ultimate Lifetime Insurance

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=2633.

Copyright © 2012 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.